

Illuminated button actuators, spring return



LPC BL10...

Flush (without mounting adapter).
Spring return.

LPC BL103	Green
LPC BL104	Red
LPC BL105	Yellow
LPC BL106	Blue
LPC BL107	Transparent



LPC BL20...

Extended (without mounting adapter)


LPC BL203	Green
LPC BL204	Red
LPC BL205	Yellow
LPC BL206	Blue
LPC BL207	Transparent




LPC BL614...

SPRING RETURN.
Ø40mm/1.6in (without mounting adapt)


LPC BL6143	Green
LPC BL6144	Red



Illuminated flush
LPC BL1...




Illuminated extended
LPC BL2...



Spring return
LPC BL614...
Illuminated spring return
LPC BL614...

Flush pushbutton with contact elements or lamp-holder



Operational characteristics

- Ambient conditions:
 - Operating temperature: -25...+70°C
 - Storage temperature: -40...+85°C
- Any mounting position is allowed.
- Degree of protection:
 - Per IEC/EN: IP66, IP67 and IP69K
 - Per UL: type 1, 2, 3R, 4, 4X, 12, 12K.

Materials

Polyamide.

Mechanical endurance

Operating force: <0.5kg / 1.1lb (actuator).
Mechanical life: 5,000,000 cycles.

Mounting adapter

Type: LPX AU120.

Actuators are installed through a Ø22mm/Ø0.89in drilling with a threaded fixing ring (Tmax = 2.3Nm / 1.69lbf).
The mounting adapter directly snaps onto the actuator.

Contact elements

Type: LPX C10 (1NO)
LPX CF10 (1NO Faston)
LPX C10A (1EM)
LPX C01 (1NC)
LPX CF01 (1NC Faston)
LPX C01D (1LB)

Contact elements snap onto the mounting adapter.

Up to 9 contact elements can be fitted on the mounting adapter: 3 on the left, 3 at the centre and 3 on the right; one on top of the other.

To mount contact elements in the centre position, use the accessory: LPX A140; see page 7-17.

Certifications and compliance

Certifications obtained: UL Listed, for USA and Canada, (File E93601), as Auxiliary Devices.
Certifications pending at time of catalogue printing: CCC.
Compliant with standards: IEC/EN 60947-1, IEC/EN 60947-5-1, UL508, CSA C22.2 n° 14.

