


ESH, Aluminum Electrolytic, 100 uF, 20%, 35 VDC, -40/+105°C, Lead Spacing = 2.5mm



Dimensions

D	6.3mm +/-0.5mm
L	11mm +1.5/-0mm
S	2.5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	20mm MIN
F	0.5mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	10000

General Information

Supplier:	KEMET
Series:	ESH
Dielectric:	Aluminum Electrolytic
Description:	Single Ended Aluminum Electrolytic
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No

Specifications

Capacitance:	100 uF
Capacitance Tolerance:	20%
Voltage DC:	35 VDC, 44 VDC (Surge)
Temperature Range:	-40/+105°C
Rated Temperature:	105°C
Life:	2000 Hrs
Dissipation Factor:	14.00% 120Hz 25C
Ripple Current:	170 mAmps (120Hz 105C)
Leakage Current:	35 uA (2min 20°C)
Impedance Ratio at -25C:	2
Impedance Ratio at -40C:	3