



## SPECIFICATION

**VOLTAGE 500VAC**  
**FREQUENCY 50/60Hz**  
**CURRENT 16A @ 40°C**  
**OVERLOAD CURRENT 150% 1MIN. 200% 1SEC**  
**TEMPERATURE -25 TO 85 °C**  
**LEAKAGE CURRENT:-**  
**AS PER IEC950 = 80mA @ 415V 50Hz**  
**HUMIDITY 90% RH**  
**VIBRATION 10-200Hz 1.8G**  
**ELECTRIC STRENGTH 2500VAC/1min.**  
**POWER LOSS (FULL LOAD) = 10W**  
**TERMINALS 4mmsq (Torque 0.5-0.6Nm)**  
**WEIGHT 1.6kg**  
**BACK MOUNTING 4x M4**  
**SIDE MOUNTING 2x M6**



## CONSTRUCTION

**PERFORATED ALUMINIUM BODY FOR AIR COOLING,**  
**ALL COMPONENTS PCB MOUNTED**

## ATTENUATION

**COMMON MODE - 80dB AT 150kHz**  
**DIFFERENTIAL MODE - 50dB AT 150kHz**

**RoHS**  
**2002/95/EC**  
  
**Compliant**