









# QUICK CONNECT BACK FITTINGS



Universal mounting of the Quick Connect electrical connector series is achieved with a variety of fittings to match the technical and commercial demands of the most harsh environment applications.

			Sealing Washer	
			Neoprene*	Centellen**
Panel mount lock nut and washer	Traditional sealing arrangement		QC205P	QC205C
Compression screw gland	Traditional sealing arrangement			
Compression screw gland with strain relief	Traditional sealing arrangement with additional strain relief			
Wire seal - 2 way Wire seal - 5 way Wire seal - 7 way Wire seal - 12 way	Economic wire sealing without the need for sealing gland. Seals on wire insulation		QC220-02 QC220-05 QC220-07 QC220-12	
Wire seal with strain relief adapter - 2 way Wire seal with strain relief adapter - 5 way Wire seal with strain relief adapter - 7 way Wire seal with strain relief adapter - 12 way	Wire seal with additional strain relief		QC225-02 QC225-05 QC225-07 QC225-12	
Wire seal with compression screw gland - 2 way Wire seal with compression screw gland - 5 way Wire seal with compression screw gland - 7 way Wire seal with compression screw gland - 12 way	Double sealing - Seals on wire insulation and outer cable sheath			
Wire seal with sealed strain relief adapter - 2 way Wire seal with sealed strain relief adapter - 5 way Wire seal with sealed strain relief adapter - 7 way Wire seal with sealed strain relief adapter - 12 way	Double sealing with additional strain relief			
Dome nut gland	Economic cable gland arrangement			

		Sealing Ring		
		Silicone	Nitrile*	Silicone**
			QC210N	QC210S
			QC215N	QC215S
			QC230N-02 QC230N-05 QC230N-07 QC230N-12	QC230S-02 QC230S-05 QC230S-07 QC230S-12
			QC235N-02 QC235N-05 QC235N-07 QC235N-12	QC235S-02 QC235S-05 QC235S-07 QC235S-12
			QC240N	QC240S

Heat Shrink	Typically used with wire seals	Details on application
Conduit adaptor	Suitable for M16 conduit adaptor	Details on application
Overmoulding	Tamperproof solutions	Details on application

\* Temperatures up to 80 Deg C  
\*\* Temperatures up to 170 Deg C

For chemical resistance  
consult Deutsch

*A step ahead in technology*

Castleham Industrial Estate  
2 Stanier Road  
St Leonards on Sea  
East Sussex  
TN38 9RP England  
Telephone +44 (0) 1424 852722  
Fax +44 (0) 1424 855979  
Email [industrial@deutsch.co.uk](mailto:industrial@deutsch.co.uk)  
[www.deutschltd.com](http://www.deutschltd.com)

