


BZV15/A0420/76 Datasheet

Product Name // Vertical Power Entry Module 72.3mm C14
Cold Condition Inlet Integral Twin Fused (PF0033) 6.3mm
Tab Termination A0420 Filter (4A PS26/A L/C v2) Double
Contact Illuminated Switch Marked I/O Red

 [View Product Page](#)





BZV01/****/** } A = 59.7 With Filter
BZV02/****/** } A = 27.4 Without Filter
BZV15/****/** } A = 59.7 With Filter
BZV16/****/** } A = 37.9 Without Filter
Panel Thickness. 1.0, 1.5, 2.0, 3.0mm.

// **Product Description:**

- Vertical Power Entry Module 58.9mm/72.3mm
 - C14 Cold Condition Inlet with integral fuseholder(s) depending on part code:
 - Part codes prefixed BZV01, BZV02: PF0011 Single Fused Inlet
 - Part codes prefixed BZV15, BZV16: PF0033 Twin Fused Inlet
 - Choice of Termination depending on part code:
 - Part codes prefixed BZV01, BZV15: 6.3mm Tab
- Part codes prefixed BZV02, BZV16: 2.8mm Tab
 - Choice of mains filter depending on part code:
 - Part codes containing /Z0000 are unfiltered
 - Choice of mains filter options (part codes containing codes starting /A)
 - Choice of many other options as specified by individual part code, including indicators, illuminated switches, switch markings, etc

// **General Information:**

Product Display Title:	Vertical Power Entry Module 58.9mm/72.3mm
Product Family:	IEC Connectors
Product Series:	Power Entry Modules
Current Max:	4A
Filter Type:	4A PS26/A L/C v2
Function:	C14 Inlets
Fuseholder Inlet Type:	Integral Twin Fused
iec Connector Components:	None
iec Connector Mates With:	PF0033
iec Filter Options:	A0420
iec Neon Colour:	Red
iec Vertical Module Height:	72.3mm
Inlet Type:	C14 Cold Condition Inlet
Switch Type:	Double Contact Marked I/O Illuminated
Voltage Max:	250V

// **Product PDF Links**

 [Power Entry Modules product data](#)

// **Product 3D CAD Model Links**

 [BZV15/A0420/763D CAD Model](#)



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)