



ADV-03 I-I4-I6-E-C2

THERMOELECTRIC MODULE



MID LEVEL PERFORMANCE - VALUE ORIENTED

3 I couple, 20x20x3.8mm, 6Amp

Features

- ROHS & REACH Compliant
- Precise temperature control
- Solid-state reliability

Applications

Automotive, Industrial,
Telecommunications, Medical, Aerospace





CHARACTERISTICS

DeltaT at 300K	[°C]	70
V _{max}	[V]	4.0
I _{max}	[A]	6.2
Q _{max}	[W]	13.7
A	[mm]	20
A _I	[mm]	20
B	[mm]	20
Flatness/Parellelism	[mm]	0.05 / 0.05





- (At hot side temperature $T_h = 25^\circ\text{C} / 298\text{K}$, under dry N_2)
- $P_c \text{ max}$ = Cooling power at $\Delta T = 0$ and $I = I_{\text{max}}$
- ΔT_{max} = Temperature difference at $I = I_{\text{max}}$ and $P_c = 0$
- Max hot side temperature $T_h = 90^\circ\text{C}$ for best long term performance
- Max mounting pressure: 1.5MPa
- Wires: UL rated wire to 105°C

ADV-03 I-14-I6-E-C2

Hot side temperature 25 degrees C



Hot side temperature 50 degrees C



ADV-03 I-14-I6-E-C2

Hot side temperature 75 degrees C

