

Switch Mode Power Supply -Intel EPS 12V- SS-400/500L1U Active PFC



www.seasonic.com



Features:

- Specification compliance: Intel EPS 12V
- DC to DC converter design
- High efficiency and reliability
- Low THD
- Low ripple & noise
- Super low noise fan control
- Short circuit protection on all outputs
- Over voltage protection
- Over power protection
- 100% hi-pot test
- 100% burn in, high temperature cycled on/off

DC Outputs:

Model	DC Outputs					Total power	Input type
	+3.3V	+5V	+12V Combined	-12V	+5Vsb		
SS-500L1U Active PFC	20A	20A	40A	0.3A	2.5A	500W	Full range
	100W ¹		480W	3.6W	12.5W		
SS-400L1U Active PFC	20A	20A	32A	0.3A	2.5A	400W	Full range
	80W ¹		384W	3.6W	12.5W		

Remarks: 1. Combined +3.3VDC & +5V DC maximum power

Dimension: L235 x W100 x H40mm
(9.3" x 3.9" x 1.6")

Connectors:

Customized modular cables

Sea Sonic Electronics Co., Ltd.
www.seasonic.com
sales@seasonic.com.tw
Tel: +886 2 2659 0338
Fax: +886 2 2659 0530

Seasonic Electronics Inc.
www.seasonicusa.com
usa@seasonic.com
Tel: +1 626 969 9966
Fax: +1 626 969 9986

Sea Sonic Europe B.V.
europe@seasonic.com
Tel: +31 (0)10-2262131
Fax: +31 (0)10-2519947

Electrical Specifications:

- Input frequency: 47/63 Hz
- Inrush current, cold start: 100A max.
- Efficiency, at normal input voltage: > 87%
- Line regulation: +/-1% typical
- Load regulation: +/-5% typical
- Cross regulation: +/-5% typical
- Ripple / noise: 1%
- MTBF, full load @ 25°C amb. : >100K hours
(Excluding the DC fan)
- Power Factor Correction: Active PFC 99% typical

Safety: CUL, TUV, CB

EMC: CE, FCC, C-tick

Specification may change without prior notice

