


ALL APN ■ AND UPC ● CODE NUMBERS SHOWN ARE PRECEDED BY THE MANUFACTURER APN OR UPC I.D. NUMBER ■ 9337103 & ● 037103.

Solid joint lineman's pliers are made of drop-forged steel with polished heads and gun metal handles. Durable, keen and induction hardened cutting edges. Available with either yellow cushion grips or Tenite butyrate grips. Crescent lineman's pliers can be supplied where indicated, with insulating grips made from Tenite butyrate. Tests have shown this material to be highly suitable for this purpose. It has a high dielectric value and we recommend pliers to which it has been applied to those who have need for insulated tools. Available on lineman's pliers where the letter "T" after the tool number is indicated (i.e. 50-7T).

The one they copy.

The Crescent 3800-CT Universal cutting plier is known throughout all industries for years of work and performance. Other brands may copy the Crescent 3800-CT, but the problem is that look-alikes can sometimes get confused with perform-alike. And that's a shame because Crescent users only want the best performance, regardless. Take the lengthened and hardened cutting jaws to allow easy cutting of flat multi-core cables. It's a clean cut in one action. The precise jaw gap allows easy wire-work and the cross checking gives sure grip of the job. Built into the handle is a hardened crimping jaw for use with 1.5mm² to 6mm² non-insulated conductors. And you can use this crimper from either side of the plier – there are no obstacles, making the job quick and easy. Check the features of the Crescent 3800-CT insulated plier, and be sure to ask for it by name – you won't be disappointed. That's the one they copy!



Finished in Australia from imported forgings.

The features in detail:



Slim line jaw with precise jaw gap.



Extended and hardened cutting jaw for use with flat multi-core cabling.



Hardened crimping jaw built into handle for use with solderless connectors.

Linesman's Pliers - Pro Series



Material Number	Description mm/in	APN/UPC	Shelf Pack
Universal Cutting Plier with Crimper		Carded	
3800CTV	200/8	■ 466817	6
Universal Cutting Plier with Crimper in Nylon Pouch			
3800CTP	200/8	■ 473709	4

- Insulated grips
- Precise jaw gap for wire work
- Cross hatch jaws for positive grip
- Serrated pipe grip

Crescent High Voltage Pliers

(Conforms to all aspects of DIN 57 680 Part 2/VDE 0680 Part 2 1978)



Universal Plier		Carded	
3800CHV	200/8	■ 473730	4
Diagonal Cutter			
5428HV	200/8	■ 321512	4
5427HV	180/7	■ 321383	4
Long Nose Plier			
6547HV	180/7	■ 365714	6

Crescent Compound Action Pliers



Linesmans Plier		Carded	
PS20509C	229/9	● 216861	3
Long Nose Plier			
PS6549C	229/9	● 216823	3
Diagonal Plier			
PS5429C	229/9	● 216847	3

- Heat treated chrome vanadium alloy steel construction
- Patented high-leverage design gives up to 60% power gain
- Special heat-treated steel spring holds jaws comfortably open
- Tested to over 1,000,000 cycles