




RoHS Compliant

REV	SIGN	DATE	DESCRIPTION	APPROVER
A0		2024.12.04	Initial Release	LENA

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

- Material:
- Item (a) Terminal Body: PA66,
 - Item (b) Terminal lever: PBT ,
 - Item (c) Terminal Cover: PA66 ,
 - Item (d) Spring: Stainless
 - Item (e) Terminal Contact: Copper alloy,

- Electrical:
- | | | |
|---|---------|---------|
| UL1059 Group B.G | Group D | Group F |
| ●Voltage rating: 300 V | 300V | 250V |
| ●Current rating: 16A | 10A | 16A |
| ●Wire range: | | |
| Solid wire: 24-12AWG | | |
| Stranded wire: 24-12AWG | | |
| ●Wire strip length: 11-13 mm | | |
| ●Withstanding Voltage: 1.6KV AC | | |
| ●Insulation Resistance: DV500V 500MΩ min | | |
| ●Operating temperature: -20°C to +105°C | | |
| ●Assembling temperature: -5°C to +105°C | | |
| ●Safety Approval:  | | |

Part No. QT xx A DP x x H xxxx G

- NO. OF POLES
- 02: 2 POLES
 - 03: 3 POLES
 - ... 24: 24 POLES
- Body color
- 0: Black
 - 1: Natural color
 - 2: Red
 - 3: Orange
 - 4: Yellow
 - 5: Green (RAL6018/T)
 - 6: Blue
 - 8: Grey (標準色)
 - 9: White
 - C: Green (RAL 6018/U)
- Lever color
- 0: Black
 - 1: Natural color
 - 2: Red
 - 3: Orange (標準色)
 - 4: Yellow
 - 5: Green (RAL6018/T)
 - 6: Blue
 - 8: Grey
 - 9: White
 - C: Green (RAL 6018/U)
- RoHS compliant (lead<4%) In copper Alloy
- 00x0: "@" Logo (Standard)
- 00xA: "ANYTEK" Mark
- Any special item by customer request. please contact sales department.

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		QT series 180D pitch 5.0mm PCB terminal block,					
PART NO.	QTxxADPx x H xxxxG			DWG NO.	8QT0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
Roy 2024.12.04	Roy 2024.12.04	Lena 2024.06.28	Lena 2024.06.28		UNIT: mm		X. ±0.50
					SCALE: 2:1		X.X ±0.30
					REV.: A0		X.XX ±0.10
SHEET: 01/01				REV.: A0		X° ±1°	