

## Features

- Maximum operating pressure is 35 bar.
- Operating temperature range -20°C to +100°C.
- Material: Steel Nickel Plated Finish
- Flow 890 l/min
- DN8.5
- ISO 6150-B-15
- Industrial Interchangeable 3/8"
- Compatible with:  
TST SWING COUPLING E  
HANSEN 4000  
PARKER 30 3/8"  
CEJN 430  
GROMELLE 900  
PARKER - RECTUS 30  
ATLAS COPCO QIC10US

## RS PRO Pneumatic Quick Connect Coupling

RS Stock No.: 0325620



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

### RS PRO Series 30 Quick Connect Couplings Plugs

Pneumatic quick-connect coupling connectors are found across industry in pneumatic systems as diverse as robotic assembly lines and other equipment.


These plugs can be used with our RS PRO 030S Series 2-Stage Security Couplings

- Maximum operating pressure is 35 bar.
- Operating temperature range -20°C to +100°C.
- Material: Steel Nickel Plated Finish
- Single Shut Off (One side is with valve)
- DN8.5
- Flow 890 l/min
- ISO 6150-B-15
- Industrial Interchangeable 3/8"
- 2-Stage Security
- Compatible with: TST SWING COUPLING E | HANSEN 4000 | PARKER 30 3/8" | CEJN 430 GROMELLE 900 | PARKER - RECTUS 30 | ATLAS COPCO QIC10US

## Specifications


|                                     |                                                                |
|-------------------------------------|----------------------------------------------------------------|
| Manufacturer Series                 | 030                                                            |
| Coupling Type                       | Quick Connect Coupling Plug                                    |
| Connection Standard                 | DN 8, ISO 4414, ISO 6150-B-15, Industrial Interchangeable 3/8" |
| Connection Standard Compatible With | HANSEN 4000; PARKER 30 3/8"; CEJN 430; GROMELLE 900; RECTUS 30 |
| Minimum Operating Temperature       | -20°C                                                          |
| Maximum Operating Temperature       | +100°C                                                         |
| Maximum Operating Pressure          | 35 bar                                                         |
| Flow                                | 890 l/min                                                      |
| Flow Direction & Sealing            | Through type coupling                                          |
| Material                            | Steel                                                          |
| Finish                              | Nickel Plated                                                  |
| Connection Type                     | Male                                                           |
| Thread Size                         | 1/4 in                                                         |
| Thread Standard                     | R                                                              |
| Thread Gender                       | Male                                                           |
| Coupling Gender                     | Male                                                           |
| Threaded Connection                 | R 1/4 Male                                                     |
| Seal material                       | N/A                                                            |
| Hose Barb Connection                | N/A                                                            |

## Specifications



| Dimensions (mm) |    |    |
|-----------------|----|----|
| SW              | L  | ØD |
| 17              | 45 | -  |

### Materials





### Material Code

A = Brass Nickel Plated


B = Zinc Plated

C = Aluminium

S = Steel Nickel Plated



### Plug Profile Serie 030



## Series 30 Quick Connect Couplings



0 - 35 bar  
(0-508 PSI)



-20° to +100°C (NBR)  
-4° to +212°F

Shut Off  
Type



OM 300 - 00700  
OM 300 - 01000  
OM 100 - 01600

FLOW

890 lt/min

DN

8.5 mm