



Main

Range	New Unica
Product or component type	Data socket
Device application	Communication
Device presentation	Mechanism
Colour tint	Anthracite (RAL 7021)
Data socket type	RJ45 8 contact(s) Cat.6 < 250 MHz
Provided equipment	Label holder Protective flap





Complementary

Communication network type	1000BASE-TX
Communication port protocol	ATM 1200 Mbps
Number of modules	1 module
Socket number	1
Type of footprint	Infraplus
Connector type	S-One
Cable shielding type	STP
Organization of wire	Shielded twisted pair
Connections - terminals	Click
Device mounting	Flush
Fixing mode	Clip-in
Installation direction	Straight
Material	Thermoplastic ABS-UV stabilised: central plate
Depth	40.5 mm
Width	22.5 mm
Height	45 mm
Embedding depth	40.5 mm
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-25...55 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins