



APC Back-UPS, 1050VA/600W Floor/Wall Mount, 230V, 8x British BS1363A outlets, USB Type A+C Port, User Replaceable Battery

BE1050G2-UK

Overview

Lead time Usually in Stock

Main

Main		
Main Input Voltage	230 V	
Other Input Voltage	220 V	
Main Output Voltage	230 V	
Other Output Voltage	220 V	
Rated power in W	600 W	
rated power in VA	1050 VA	
Product or component type	Uninterruptible power supply (UPS)	
Input Connection Type	BS1363A British	
output connection type	6 BS 1363 2 BS 1363 surge	
Battery type	Lead-acid battery	
Provided equipment	User manual	
Range of product	Back-UPS	

Batteries & Runtime

Run Time	View Runtime Graph ☐	
Efficiency	View Efficiency Graph ☐	
Number of battery filled slots	0	
Number of battery free slots	0	
Battery recharge time	6 h	
Battery voltage	12 V	
Battery capacity	9.0 Ah	
Battery charger power	7 W rated	
Battery power in VAH	80 VAh runtime	
Battery life	25 year(s)	
Extended runtime	0	

General

Number of power module free 0 slots

Number of power module filled slots	0
Redundant	No

Physical

Colour	Black	
Height	12 cm	
Width	13 cm	
Depth	36.5 cm	
Net weight	4.6 kg	
Mounting preference	No preference	
Mounting mode	Not rack-mountable	
Two post mountable	0	
USB compatible	Yes	

Input

Network frequency	4763 Hz
Input voltage limits	180266 V
Maximum input current	6 A
Switching current capacity	10 A

Output

Maximum configurable power in W	600 W	
Output frequency	4763 Hz 50/60 Hz +/- 1 Hz sync to mains Unsynchronised	
UPS type	Standby	
Wave type	Stepped approximation to a sinewave	
Efficiency	80 % (full load)	
Graph start point	40	
Maximum configurable power in VA	1050 VA	
Transfer time	6 ms typical : 10 ms maximum	

Conformance

Product certifications	CE EAC
Standards	EN/IEC 62040-1:2019/A11:2021
	EN/IEC 62040-2:2006/AC:2006
	EN/IEC 62040-2:2018

Environmental

Ambient air temperature for operation	040 °C
Relative humidity	090 %
Operating altitude	03000 ft
Ambient air temperature for storage	-1545 °C

Storage Relative Humidity	095 %	
Storage altitude	0.00000000004572.0000000000 m	
Acquetic level	45 dBA	

Communications & Management

Control panel	LED status display with on line : on battery : replace battery and overload indicators	
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm	
control panel	LED status display with load and battery bar-graphs and on line : on battery : replace battery : and overload indicators	

Surge Protection and Filtering

Surge energy rate 310 J

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19 cm
Package 1 Width	44.1 cm
Package 1 Length	18.6 cm
Package 1 Weight	4.4 kg
SCC14	10731304738302

Logistical informations

Country of origin PH

Contractual warranty

Warranty

2 years repair or replace, 3 years repair or replace for European Union countries



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	No

BE1050G2-UK

Image of product / Alternate images

Alternative



