

RUSH+ 2.0 XP

PROTECTION & EFFICIENCY

The RUSH+ 2.0, our iconic model, is designed to withstand the harshest work environments, making it a trusted choice for all professionals. While RUSH+ 2.0 is recognised for its comfortable wear thanks to a best-in-class fit, RUSH+ 2.0 XP goes beyond by also offering extended protection and support thanks to its replaceable foam gasket and adjustable strap. RUSH+ 2.0 XP is made with 27% of recycled materials. Its wide lens, coated with our exclusive Platinum anti-fog and anti-scratch solution optimise the wearer's vision.

49 G

- + **COMFORTABLE FIT:
ERGONOMIC TEMPLES & HINGES**
- + **ENHANCED PROTECTION & SUPPORT:
REPLACEABLE FOAM SEAL & STRAP**
- + **OPTIMAL VISION:
PLATINUM COATED**
- + **SUSTAINABLE:
MADE OF 27% RECYCLED MATERIAL**



TECHNOLOGIES

CSP
PLATINUM

VERSIONS

REGULAR SIZE M/L



SMALL SIZE S



ACCESSORIES



bolle
SAFETY

AVAILABLE IN ECO-POLYBAG
GO GREEN

RUSH+ 2.0 XP **PACKAGING & EAN13 CODE**

USE	VERSION	SIZE	REFERENCE	LENS MARKING	FRAME MARKING <small>F: Glasses / B: Glasses with foam and strap kit</small>	COATING	STANDARD	SINGLE: <small>Size: 29.5 x 12 x 7 cm</small>	INNER BOX: <small>Size: 27.5x18x 1313 cm Weight: 0.6150.765 kg</small>	OUTER PACK: <small>Size: 58 x 38 x 30 cm Weight: 6.82 kg</small>
	CLEAR	M/L	RUSXMN10E	UL1,2 CT 1 KN C€	16321 CT 1-M C€	PLATINUM	EN ISO 16321-1	3660740023706	3660740123703 -10 pcs	3660740223700 -80 pcs
	SMOKE	M/L	RUSXMN20E	GL3 CT 1 KN C€	16321 CT 1-M C€	PLATINUM	EN ISO 16321-1	3660740023737	3660740123734 -10 pcs	3660740223731 -80 pcs
	COPPER	M/L	RUSXMN30E	GL1 CT 1 KN C€	16321 CT 1-M C€	PLATINUM	EN ISO 16321-1	3660740023768	3660740123765 -10 pcs	3660740223762 -80 pcs
	CLEAR	S	RUSXSN10E	UL1,2 CT 1 KN C€	16321 CT 1-S C€	PLATINUM	EN ISO 16321-1	3660740023829	3660740123826 -10 pcs	3660740223823 -80 pcs

OPTIONAL ACCESSORIES

FOAM AND STRAP KIT	M/L	RUSXMN70E	C€	3660740023799	3660740123796 -10 pcs	3660740223793 -10 pcs
FOAM AND STRAP KIT	S	RUSXSN70E	C€	3660740023850	3660740123857 -10 pcs	3660740223854 -10 pcs
RETAINER STRAP	PSPUNISS01			3660740011970	3660740111977 -40 pcs	3660740211974 -480 pcs

BOLLÉ SAFETY PRODUCT APPROVAL CERTIFICATES TO C€ STANDARDS WILL BE SENT ON REQUEST.

CUSTOM CODE: 9004901000



GENERAL SPECIFICATIONS

LENS	POLYCARBONATE - 2.2 MM	FOAM	SBR
CURVE	8 - VERY CURVED	STRAP	NYLON POLYESTER - 16MM
FRAME	RECYCLED PC/TPR - RIMLESS	OPTIONAL	FOAM AND STRAP KIT



CLEANING & STORAGE

CLEANING: The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

STORAGE: All products must be stored in a dry and clean environment.



MADE IN: TW

DATASHEET: 02-20-2025

bolle-safety.com

Europe Headquarters
34 rue de la Soie
69100 Villeurbanne
France
P : 00 33 (0) 4 78 85 23 64

U.K. & Ireland
Unit C83 - Barwell Business Park
Leatherhead Road - Chessington
Surrey - KT9 2NY - UK
P : 00 44 (0)208 391 4700

USA Office
2810 Caribou Court, Suite 160
Carlsbad, CA 92010
United States of America
P : 800 222 6553

Asia-Pacific Office
32-40 Fairchild Street
Heatherton VIC 3202
Australia
P : 1300 138 098



PACKAGING

ECO-POLYBAG

Available on all Bollé Safety's eyewear (except B-Line: 50% recycled)



PRODUCT



27.3%

OF THIS EYEWEAR IS RECYCLED

0.6362 kgCO₂e EMISSIONS FOR ONE PRODUCT LIFE CYCLE

22.4% CO₂ REDUCTION VS THE SAME STANDARD PRODUCT

SOURCES :
ECOINVENT V3.8
(01/07/2024)

*8.7% reduction thanks to ECO-POLYBAG for 10 units in FSC-certified cardboard packaging compared with standard polybags packaged in non-FSC cardboard.

**27.8% reduction thanks to ECO-PACK compared to standard inner packaging in a non-FSC cardboard.

	 S	 M/L	 M/L	 M/L
VERSIONS	RUSXSN10E	RUSXMN10E	RUSXMN20E	RUSXMN30E
FRAME/TEMPLES COMPOSITION	RECYCLED POLYCARBONATE	RECYCLED POLYCARBONATE	RECYCLED POLYCARBONATE	RECYCLED POLYCARBONATE
LENS COMPOSITION	RECYCLED POLYCARBONATE	RECYCLED POLYCARBONATE	RECYCLED POLYCARBONATE	RECYCLED POLYCARBONATE
% OF TOTAL PRODUCT WEIGHT	28.6%	27.3%	27.3%	27.3%
CO ₂ Footprint	0,6302 kgCO ₂ e	0,6362 kgCO ₂ e	0,6362 kgCO ₂ e	0,6362 kgCO ₂ e
CO ₂ reduction VS standard product	21.2%	22.4%	22.4%	22.4%