


Magnifier Luminaire




SNL 319 A

connected load	230 V; 50 Hz
fitted with	3 x compact fluorescent lamp TC-S 9 W neutral white
work equipment	conventional ballast
mains lead	approx. 3.0 m; shock-proof plug
luminaire body	plastic
material	ESD-version
surface	
tubular sections	steel tube
material	ESD-coat of lacquer
surface	
weight (net)	approx. 4,4 kg
fastening	screw-down flange~table clamp (accessory)~wall bracket (accessory)
technology	multi-stage switchable
usage	switch
lamp cover	screen; milky
balance of articulation joints	spring
class of protection	I
colour luminaire body	black
colour of tubular sections	black
lens; dimensions	162 x 105
lens; diopters	3
special features	light output controlled with 2-way-switch,
article no.	112128000



E_{min}: 1967 lx
E_m: 4252 lx
E_{max}: 6096 lx



measuring conditions: d=15cm

