

ENGINEER OF LIGHT.



fitted with

work equipment connected load power consumption luminous flux luminous efficacy light distribution light colour

color rendering index (CRI)

glare-free

system of protection class of protection

technology

usage luminaire body

lamp cover tubular sections

balance of articulation joints

weight (net) mains lead

fastening

special features

LED

Energy efficiency category A+

without

12-28V AC and 12-40V DC

approx. 8.5 W approx. 600 lm approx. 7 lm/W

direct, narrow-angled beam neutral white, approx. 5000 K

> 80 screen IP 67 Ш

switchable, continuously dimmable

push button

aluminium, anodised, black

glass screen

tubular aluminium section, anodized, black

spring approx. 1.6 kg

approx. 3 m; with free stranded wires

screw-down flange, table clamp (accessory), wall bracket

(accessory)

Spot with a 10° angle of radiation

 ϵ



illuminance

distance: 50 cm 5088 lx 30053 lx 682 lx 30 cm 25 20 15 25 10 15 20

luminous intensity



