

**640751-1**

✓ ACTIVE

**Appliance Connectors**


TE Internal #: 640751-1

Loose Piece, Unplated Plating, -40 – 200 °C [-40 – 392 °F],

Appliance Connectors

[View on TE.com >](#)

Terminals &amp; Splices &gt; Special Purpose Terminals



Terminal Material Thickness: .51 mm [.02 in]

Terminal Plating Material: **Unplated**Packaging Method: **Loose Piece**Sealable: **No**

Operating Temperature Range: -40 – 200 °C [-40 – 392 °F]

**Features****Product Type Features**

Terminal Features	Heavy Duty
Sealable	No

**Contact Features**

Terminal Plating Material	Unplated
---------------------------	----------

**Dimensions**

Terminal Material Thickness	.51 mm[.02 in]
-----------------------------	----------------

**Usage Conditions**

Operating Temperature Range	-40 – 200 °C[-40 – 392 °F]
-----------------------------	----------------------------

**Packaging Features**

Packaging Quantity	1
Packaging Method	Loose Piece

**Product Compliance**[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


## Compatible Parts



## Also in the Series | Appliance Connectors






Crimp Terminal Housings(1)



Special Purpose Terminals(10)

## Customers Also Bought

TE Part #114017-ZZ  
SEALING PLUG, SIZE 12/16, WHTTE Part #CAT-D48-ST273  
DEUTSCH Solid ContactsTE Part #DT06-2S  
PLG, 2P, GRY, NTE Part #DT04-2P  
REC, 2P, GRY, NTE Part #CAT-D487-W416  
Wedgelocks: DEUTSCH DTTE Part #281934-2  
SINGLE WIRE SEALTE Part #CAT-AM71-CH8172  
AMP SUPERSEAL 1.5MM,  
CONNECTOR HOUSING

## Documents

### Product Drawings

#### HEAVY DUTY BURNER CLIP ST

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_640751-1\\_AK.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_640751-1\\_AK.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_640751-1\\_AK.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Product Specifications****Product Specification**

English

---

**Agency Approvals****UL Report**

English