


TASE40-XL-N

Plummer block housing unit

Plummer block housing units TASE, cast iron housing, radial insert ball bearing with eccentric locking collar, T seals

X-life

Technical information



Your current product variant

Material	GG	Grey cast iron
Groove	N	Cast iron housing with undercut slot for end caps
Material	GG	Cast iron

Main Dimensions & Performance Data

d	40 mm	Bore diameter
L	179 mm	Length total
H <sub>2</sub>	99 mm	Height
≈m	1.96 kg	Weight

Mounting dimensions

J	138.25 mm	Distance fixing bore
N	14 mm	Width (slot)
N <sub>1</sub>	26 mm	Length (slot)



Dimensions

H	49.2 mm	Distance shaft axis
A	48 mm	Width (base)
A <sub>1</sub>	30 mm	Width (head)
H <sub>1</sub>	19 mm	Heigth (base)
B <sub>1</sub>	56.5 mm	Locking collar total width
S <sub>1</sub>	35.1 mm	Distance of raceway to locking collar
Q	M6	Connection thread for lubrication

Additional information

ASE08	Housing
GE40-XL-KTT-B	Bearing designation
KASK08	Protecting cap

Temperature range

T <sub>min</sub>	-20 °C	Operating temperature min.
T <sub>max</sub>	120 °C	Operating temperature max.