

## Features

- Standard Oilite® bearings are impregnated with highly refined mineral oil to ISO VG (SAE 30) having a high viscosity index and containing anti-oxidant, anti-rust and defoamant additives.
- A wide range of lubricants are available to meet specific requirements within a temperature range of -60°C to 200°C.
- Standard Oilite® oil retaining tin bronze is the generally specified material. It gives a good balance between strength, wear resistance, conformability, and durability in operation. Ideal in a wide variety of applications where self-lubricating properties are required over a long period of time.

## RS PRO Oilite® Plain Bearing

RS Stock No.: 0528812



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

RS PRO is offering range of Oilite® plain bearings – self-lubricating bearings that are made from metal alloys with pores that channel lubricants between the bearing itself and the shaft.

- Standard Oilite® bearings are impregnated with highly refined mineral oil to ISO VG (SAE 30) having a high viscosity index and containing anti-oxidant, anti-rust and defoamant additives.
- Lubricant : Shell Tellus S2 MX68
- Temperature range of -15°C to +75°C.
- Standard Oilite® oil retaining tin bronze is the generally specified material. It gives a good balance between strength, wear resistance, conformability, and durability in operation. Ideal in a wide variety of applications where self-lubricating properties are required over a long period of time.
- All dimensions and tolerances of our metric ranges conform to ISO 2795:1991
- Wide range of metric and imperial sizes
- Wide range of different types: Plain, Flanged

\* Below dimensions in mm



## Specifications

### Details

|                 |                 |                |      |        |   |
|-----------------|-----------------|----------------|------|--------|---|
| Inner Diameter  | 0.75            | Outer Diameter | 1.25 | Length | 2 |
| Tolerance Range | Imperial (Inch) |                |      |        |   |

### Material Specification

|                                        |                                          |                         |     |
|----------------------------------------|------------------------------------------|-------------------------|-----|
| Structure                              | Oil impregnated sintered bronze*         |                         |     |
| Max PV (N/mm² x m/s)                   | 1.8                                      | Max Static load (N/mm²) | 50  |
| Max Dynamic load (N/mm²)               | 14                                       | Max Sliding speed (m/s) | 5   |
| Operating temperature (°C)             | -60 to 200*<br>*dependant on lubrication | Density (g/cm³)         | 6.6 |
| Radial crushing strength (K Min M/mm²) | 160                                      |                         |     |

### Tolerances & Fittings (Imperial)

|                   | Min   | Max   | Tolerance |
|-------------------|-------|-------|-----------|
| Inside Diameter   | 0.752 | 0.753 |           |
| Outside Diameter  | 1.252 | 1.253 |           |
| Overall Length    | 1.993 | 2.008 |           |
| Concentricity Max | 0.003 | 0.003 |           |

