



SAFETY DATA SHEET

ULTRACUT EVO 280

Page: 1

Compilation date: 24/11/2014

Revision date: 29/10/2019

Revision No: 10

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: ULTRACUT EVO 280

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Water miscible metalworking fluid

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Eye Dam. 1: H318; Aquatic Chronic 3: H412; Skin Irrit. 2: H315

Most important adverse effects: Causes skin irritation. Causes serious eye damage. Harmful to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: H315: Causes skin irritation.

H318: Causes serious eye damage.

H412: Harmful to aquatic life with long lasting effects.

Hazard pictograms: GHS05: Corrosion



Signal words: Danger

[cont...]

SAFETY DATA SHEET

ULTRACUT EVO 280

Page: 2

Precautionary statements: P280: Wear protective gloves/protective clothing/eye protection/face protection.
P302+P352: IF ON SKIN: Wash with plenty of water.
P305+P351+P338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310: Immediately call POISON CENTER/doctor.
P362+P364: Take off contaminated clothing and wash it before reuse.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

ALCOHOLS C16-C18, C18-UNSATURATED, ETHOXYLATED (<2,5 EO) - REACH registered number(s): 01-2119489407-26

EINECS	CAS	PBT / WEL	CLP Classification	Percent
500-236-9	68920-66-1	-	Skin Irrit. 2: H315; Aquatic Chronic 2: H411	5-10%

ALKENYL ALKANOL AMIDE - REACH registered number(s): 01-2119968565-22

271-653-9/700-972-2	68603-38-3	-	Skin Irrit. 2: H315; Eye Irrit. 2: H319; Aquatic Chronic 2: H411	5-10%
---------------------	------------	---	--	-------

ALKOXYAMINE - REACH registered number(s): 01-2119488930-28

203-868-0	111-42-2	-	Acute Tox. 4: H302; Skin Irrit. 2: H315; Eye Dam. 1: H318; STOT RE 2: H373	1-5%
-----------	----------	---	--	------

CARBOXYMETHYLATED POLYGLYCOL ETHER - REACH registered number(s): EXEMPT - POLYMER

-	57635-48-0	-	Skin Irrit. 2: H315; Eye Dam. 1: H318	0.5-1%
---	------------	---	---------------------------------------	--------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Transfer to hospital for specialist examination.

Ingestion: Wash out mouth with water. Do not induce vomiting. If conscious, give half a litre of water to drink immediately. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be pain and redness. The eyes may water profusely. There may be severe pain. The vision may become blurred. May cause permanent damage.

[cont...]

SAFETY DATA SHEET

ULTRACUT EVO 280

Page: 3

Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers. Carbon dioxide. Alcohol or polymer foam. Alcohol resistant foam. Dry chemical powder.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Mark out the contaminated area with signs and prevent access to unauthorised personnel. Do not attempt to take action without suitable protective clothing - see section 8 of SDS.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Avoid the formation or spread of mists in the air.

[cont...]

SAFETY DATA SHEET

ULTRACUT EVO 280

Page: 4

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Tightly fitting safety goggles. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Environmental: No special requirement.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Yellow-brown

Odour: Characteristic odour

Evaporation rate: Negligible

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Miscible

Viscosity: Viscous

Boiling point/range°C: 100

Melting point/range°C: No data available.

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: > 100

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: > 200

Vapour pressure: No data available.

Relative density: 0.95

pH: No data available.

VOC g/l: 0

9.2. Other information

Other information: Not applicable.

[cont...]

SAFETY DATA SHEET

ULTRACUT EVO 280

Page: 5

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

ALCOHOLS C16-C18, C18-UNSATURATED, ETHOXYLATED (<2,5 EO)

ORAL	RAT	LD50	> 2000	mg/kg
------	-----	------	--------	-------

ALKENYL ALKANOL AMIDE

DERMAL	RBT	LD50	>2000	mg/kg
ORAL	RAT	LD50	>3000	mg/kg

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be pain and redness. The eyes may water profusely. There may be severe pain. The vision may become blurred. May cause permanent damage.

Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur.

[cont...]

SAFETY DATA SHEET

ULTRACUT EVO 280

Page: 6

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Other information: Not applicable.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

ALCOHOLS C16-C18, C18-UNSATURATED, ETHOXYLATED (<2,5 EO)

FISH	96H LC50	>1	mg/l
------	----------	----	------

ALKENYL ALKANOL AMIDE

DAPHNIA	48H EC50	55	mg/l
FISH	96H LC50	1460	mg/l

12.2. Persistence and degradability

Persistence and degradability: No data available.

12.3. Bioaccumulative potential

Bioaccumulative potential: No data available.

12.4. Mobility in soil

Mobility: No data available.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity. Harmful to aquatic organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Recovery operations: Not applicable.

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

[cont...]

SAFETY DATA SHEET

ULTRACUT EVO 280

Page: 7

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H302: Harmful if swallowed.

H315: Causes skin irritation.

H318: Causes serious eye damage.

H319: Causes serious eye irritation.

H373: May cause damage to organs ({{{0||message=<or state all organs affected, if known>||filter=(_)?ORGAN_.+}}}) through prolonged or repeated exposure ({{{1||message=<state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard>||filter=(_)?EXP_ROUTE_.+}}}).

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.