



CST

TE Internal #: 2-1375820-4

Housing, Receptacle, Crimp, Wire-to-Wire, UL 94V-0, 24 Position, 2.54 mm [.1 in] Centerline, 1 Row, Rectangular Wire & Cable Connectors & Housings

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors > Receptacle Housing: 2.54mm, 1 Row, CST-100 II



Connector Product Type: **Housing**

Mating Retention Type: **Latch**

Connector System: **Wire-to-Wire**

Contact Retention Within Housing: **Without**

UL Flammability Rating: **UL 94V-0**

[All Receptacle Housing: 2.54mm, 1 Row, CST-100 II \(24\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	24
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Type	Socket
Contact Retention Within Housing	Without



Contact Current Rating (Max)	7 A
------------------------------	-----

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
Mating Retention Type	Latch
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon - GF
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Connector Height	6.6 mm[.26 in]
Wire Size	26 – 22 AWG
Connector Length	61.47 mm[2.42 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JAN 2025  
(247)  
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-643075-4  
24P MTA100 MOLDED COVER




TE Part # 2-640456-4  
24P MTA100 HDR ASSY F/L SQ STR




TE Part # 2-640454-4  
24P MTA100 HDR ASSY SQ STR POL


Customers Also Bought




TE Part #1445336-1  
LOOSE PC CONTACT TIN PLATED



TE Part #42741-2  
250 FASTON,REC.,18-14,TPBR



TE Part #130517  
PIDG 22-16 SPADE M4




TE Part #1-320551-4  
TERMINAL,PIDG R IR 18 8



TE Part #42660-2  
250 FASTON REC 18-14 AWG TPBR



TE Part #556879-2  
PLUG HSG,AMPINNERGY WTB,2 POS



TE Part #1-770849-2  
12P SL156 HSG W/LCK RMP & TABS



TE Part #CAT-104CST-RCPHS  
Receptacle Housing: 2.54mm, 1 Row, CST-100 II



TE Part #NB18792001  
RNF-100-1/16-CL-STK

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-1375820-4\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-1375820-4\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-1375820-4\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

CSA Certificate

English