

Product datasheet

Specifications



Acti9 iC60H 4P 1A B Miniature Circuit breaker

Local distributor code:
396790710 A9F53401

EAN Code: 3606480514562

Main

Range	Acti9
product name	Disbo iC60
Product or component type	Miniature circuit-breaker
Device short name	iC60H
Poles description	4P
Number of protected poles	4
[In] rated current	1 A
Network type	AC/DC
Trip unit technology	Thermal-magnetic
Curve code	B
Breaking capacity	70 kA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 70 kA Icu at 12...133 V AC 50/60 Hz conforming to EN/IEC 60947-2 70 kA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 50 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA Icu at 220...250 V DC conforming to EN/IEC 60947-2 10000 A Icn at 400 V AC 50/60 Hz conforming to EN/IEC 60898-1
Utilisation category	Category A conforming to EN/IEC 60947-2

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	12...133 V AC 50/60 Hz 220...240 V AC 50/60 Hz 380...415 V AC 50/60 Hz 440 V AC 50/60 Hz 400 V AC 50/60 Hz 220...250 V DC
Magnetic tripping limit	4 x In +/- 20 %
[Ics] rated service breaking capacity	70 kA 100 % conforming to EN/IEC 60947-2 - 220...240 V AC 50/60 Hz 70 kA 100 % conforming to EN/IEC 60947-2 - 12...133 V AC 50/60 Hz 70 kA 100 % conforming to EN/IEC 60947-2 - 380...415 V AC 50/60 Hz 50 kA 100 % conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 7500 A 75 % conforming to EN/IEC 60898-1 - 415 V AC 50/60 Hz 10 kA 100 % conforming to EN/IEC 60947-2 - 100...133 V DC
Limitation class	3 conforming to EN/IEC 60947-2
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-2
Contact position indicator	Yes
control type	Toggle

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Local signalling	Trip indicator
Mounting mode	Clip-on
Mounting support	Rail
9 mm pitches	8
Height	85 mm
Width	72 mm
Depth	78.5 mm
Product weight	0.5 kg
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Provision for padlocking	Padlockable
Connections - terminals	Single terminal (top or bottom) 1...25 mm ² rigid Single terminal (top or bottom) 1...16 mm ² flexible
Wire stripping length	14 mm for top or bottom connection
Tightening torque	2 N.m top or bottom
Earth-leakage protection	Separate block

Environment

Standards	EN/IEC 60898-1 EN/IEC 60947-2
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 60947-2
Overvoltage category	IV
Tropicalisation	2 conforming to IEC 60068-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	7.5 cm
Package 1 Length	9.0 cm
Package 1 Weight	443.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	3
Package 2 Height	8.0 cm
Package 2 Width	9.5 cm
Package 2 Length	22.0 cm
Package 2 Weight	1.384 kg

Unit Type of Package 3	S03
Number of Units in Package 3	33
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	15.711 kg

Logistical informations

Country of origin	BG
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	42
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
SCIP Number	26ff71d1-98cf-4280-8725-455b9a6b2fb9
REACH Regulation	REACH Declaration

Use Again

 Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins