

PUSH-IN TERMINAL, FEED THROUGH, 4 POINTS, 4MM², BLUE

NSYTRP44BL

Local distributor code:

397149250

EAN Code: 3606480533334

Main

Range	Linergy
product name	Linergy TR
Product or component type	Terminal block
Device short name	TRP
Accessory / separate part category	Connection accessory
Terminal block type	Passthrough
Terminal block level	1
Mounting mode	Clip-on
Nominal cross section	4 mm²
Length	77 mm
Colour	Blue
Quantity per set	Set of 50

Complementary

Width	6.2 mm	
Hatala		
Height	36.5 mm	
Connections - terminals	2 x push-in: downstream	
	2 x push-in: upstream	
number of connections	4	
Connection position	Тор	
Number of measurement input	2	
Cable cross section	0.24 mm², flexible without cable end	
	0.26 mm², solid with cable end	
	0.84 mm², flexible with cable end	
	0.24 mm², solid without cable end	
Wire stripping length	12 mm	
Tool type	Connection: without tool	
	Disconnection: flat screwdriver	
[Ue] rated operational voltage	800 V conforming to EN/IEC 60947-7-1	
	600 V CSA	
	600 V UL	
[In] rated current	32 A conforming to EN/IEC 60947-7-1	
	30 A CSA	
	30 A UL	

Material	Polyamide 6/6: insulating case	
	Copper alloy: connector and screw	
	Copper alloy: commoning link	
	Chromium-nickel steel: spring	
Dielectric loss	0.01 at 1 MHz conforming to IEC 60250	
	0.01 at 1 MHz conforming to VDE 0303-T4	
Dielectric constant	3.7 at 1 MHz	
Resistivity	10000 MΩ.m conforming to IEC 60093	
	10000 MΩ.m conforming to VDE 0303-T30	
Surface resistance	1000 GΩ conforming to IEC 60093	
	1000 G Ω conforming to VDE 0303-T30	
Creep resistance	500 CTI (> 400 kB) conforming to IEC 60093	
	500 CTI (> 400 kB) conforming to VDE 0303-T30	
Flame retardance	V0, thickness0.8 mm conforming to UL 94	
Net weight	14.2 g	
Range compatibility	PrismaSeT G	
	PrismaSeT P	
	PrismaSet HD	
	PrismaSeT Pack 250	
	PanelSeT	
	Mureva	
	PrismaSeT XS	
	TeSys	
Product compatibility	Spacial enclosures	
Environment		
Product certifications	GL	
	UL	
	CSA	
Dielectric strength	1000 V conforming to IEC 60243-1	
Ambient air temperature for	-40130 °C conforming to IEC 60216-1	
operation	-40130 °C conforming to VDE 0304-T21	
Packing Units		
Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Deelsens 4 Heimbl	5.0	

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	7.0 cm
Package 1 Length	27.0 cm
Package 1 Weight	14.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	50
Package 2 Height	5.0 cm
Package 2 Width	7.0 cm
Package 2 Length	27.0 cm
Package 2 Weight	757.0 g

Logistical informations

Country of origin

Contractual warranty

Warranty

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	6
Environmental Disclosure	Product Environmental Profile

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
Halogen content performance	Halogen free plastic parts product

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No