

83 Pipe Wrenches 90°



DIN 5234


- ▶ Swedish pattern
- ▶ 90° angled jaws
- ▶ jaws with offset teeth in opposite direction
- ▶ teeth additionally induction hardened
- ▶ T-beam handle design
- ▶ captive adjusting nut

- ▶ red powder coated, jaws bright ground
- ▶ forged
- ▶ Chrome Vanadium steel, oil-hardened and tempered



83 10 015

Article-No.	EAN-Code 4003773-	Capacity Inch	Working capacity		Length	
			mm	mm	mm	g
83 10 010	014188	1	0 - 42	310	785	
83 10 015	014195	1 1/2	0 - 60	420	1425	
83 10 020	014201	2	0 - 70	560	2590	
83 10 030	022329	3	10 - 105	650	3450	
83 10 040	022336	4	10 - 130	750	4910	



83 Pipe Wrenches 45°



DIN 5234


- ▶ Swedish pattern
- ▶ 45° angled jaws
- ▶ jaws with offset teeth in opposite direction
- ▶ teeth additionally induction hardened
- ▶ T-beam handle design

- ▶ captive adjusting nut
- ▶ red powder coated, jaws bright ground
- ▶ forged
- ▶ Chrome Vanadium steel, oil-hardened and tempered



83 20 015

Article-No.	EAN-Code 4003773-	Capacity Inch	Working capacity		Length	
			mm	mm	mm	g
83 20 010	014218	1	0 - 42	320	810	
83 20 015	014225	1 1/2	0 - 60	430	1490	
83 20 020	014232	2	0 - 70	570	2820	



83 Pipe Wrenches S-Type



DIN 5234

- ▶ slim, S-type jaw design, 45° angled jaws
- ▶ jaws with offset teeth in opposite direction
- ▶ teeth additionally induction hardened
- ▶ three-point gripping on pipes, self-locking

- ▶ T-beam handle design
- ▶ captive adjusting nut
- ▶ red powder coated, jaws bright ground
- ▶ forged
- ▶ Chrome Vanadium steel, oil-hardened and tempered



83 30 015

Article-No.	EAN-Code 4003773-	Capacity Inch	Working capacity		Length	
			mm	mm	mm	g
83 30 005	025221	1/2	0 - 35	245	500	
83 30 010	014249	1	0 - 42	320	870	
83 30 015	014256	1 1/2	0 - 60	420	1570	
83 30 020	014263	2	10 - 70	540	2540	
83 30 030	014164	3	10 - 120	680	4295	

