

8567-10

Torque wrench DREMOMETER

60-300 Nm / 45-220 lbf-ft

Code	ETIM
7685960	EC002132
EAN	UNSPSC
4002805856710	27-11-17-15
Country of origin	eCl@ss
Germany	21-04-02-22
Customs tariff number	
82041100	



Article description

- Use:
- Controlled screw tightening in the range of 60 - 300 Nm / 45 - 220 lbf-ft
- For use in almost all industrial manufacturing areas
- Features:
- Classified according to DIN EN ISO 6789-2:2017 Type II Class A, incl. traceable test certificate, calibrated to a maximum permissible deviation of +/- 3 % and thus more precise than the +/- 4 % required by the standard
- 1/2" square drive with ball locking device as per DIN 3120 - A 12.5, ISO 1174
- Automatic short-path actuation with tactile impulse and audible signal
- Dual scale with a scale graduation of 5 Nm and 5 lbf-ft
- With push button release
- Technical advantage/Function:
- Lightweight yet robust (as the housing is made of an aluminium alloy) and resilient, very workshop-friendly
- No inaccuracies whether used with both hands or held away from the handle (as for standard torque wrenches)
- Both the square drive and fulcrum are on an axis which ensures a high degree of user safety; can be extended to reduce the user's working load.
- Extremely low wear attributable to reduced forces in a lever mechanism
- Forged lever chain from our group own quality forge
- Maximum precision even when subjected to extreme continuous use • Long life cycles and tool lives
- Easy operation - fast and safe torque tightening
- Easy adjustment thanks to attractive adjusting button secured against loss at the end of the handle
- Single- and double-square drive for controlled bi-directional tightening

Article information

Contents (Qty of pieces)	1	Torque range (min./max.) [lbf-ft]	45 lbf-ft - 220 lbf-ft
Net weight [kg]	2,3 kg	Trigger mechanism	Short path triggering
Total length [mm]	617 mm	Precision +/-	+/- 3 %
Total width [mm]	35 mm	Direction of tightening	Left and right
Total height [mm]	48 mm	Fixed setting	no
Material	Aluminum alloy	Test certificate	DIN EN ISO 6789-2:2017
Standard	DIN 3120 - B 20 ISO 1174	Head height l [mm]	30 mm
Drive connector square (male)	1/2"	Width of head l [mm]	35,0 mm
Drive connector square (male)	12,5 mm	Torque wrench type	CL
Drive type/drive	Double square rigid	Calibration length	529 mm
Torque (min.) [N·m]	60 Nm	Graduation [lbf-ft]	5 lbf-ft
Torque (max.) [N·m]	300 Nm	Graduation [n·m]	5 Nm
Torque (min.) [lbf-ft]	45 lbf-ft	Distance housing - square drive	17,5 mm
Torque (max.) [lbf-ft]	220 lbf-ft	Storage/Content	Plastic box
Torque range (min./max.) [N·m]	60 Nm - 300 Nm		