



B 400 SK

E0845236

Splice KSF, 400mm2



Product Properties:

Suitable for Class 5 conductor	Yes
Suitable for Class 6 conductor	Yes
Model	UL model
Max. current (Imax)	631 A
Number of branches	0 N/A
Insulation	None
Colour insulation	N/A
Sleeve form	Short
Suitable for solid cores	Yes
Suitable for stranded conductors	Yes
Suitable for fine strand conductors	Yes
Suitable for high temperatures (to 650 °C)	No
Suitable for insulated varnish	No
Suitable for round conductors	Yes
Suitable for flat conductors	No
For pull protected connections	No
Voltage level	Up to 35 kV
Type of connection	Other
Oil stop/centre bar	No
Max Temp	150 °C
Surface protection	Tinned
Material	Copper

Series	KRF/KSF (10-500mm2)
--------	---------------------

Dimensions:

ID	30 mm
OD	36 mm
L	75 mm
MOQ	25 .
Unit	pcs
Nominal cross section	400 mm²
Series	KRF/KSF (10-500mm2)

Approvals:

Approved according to CE	Yes
Approved according to UKCA	Ja
Approved according to DNV	Yes

Compliance:

Conflict Minerals	Contain "Tin"
Extended Minerals	Contain "Copper"
PFAS	No PFAS
REACH	No SVHC (Latest. 05 Nov 2025)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable

Other information:

ETIM-Class	EC001059 - Crimp splices for copper conductor
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Copper tube Splices
Search Description	RÖRSKARVHYLSA KSF
Alternative SKU	B400SK
E-no	E0845236

Logistic information:

Barcode	733117612228
Country of origin	CN
E-no	E0845236
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	25 .
Stock code	B 400 SK
Taric code	85369010
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.

Nelco Contact AB - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - order@nelco.se - www.nelco.se