

# Product datasheet

Specifications



## switch disconnecter iSW - 3P - 100 A - 415 V

Local distributor code:

399368330

A9S66391

EAN Code: 3606480531446

## Main

Range	Acti9
Product name	Acti9 iSW
Product or component type	Switch disconnecter
Device short name	iSW
Device application	Isolation Control
Poles description	3P
Utilisation category	AC-22A
Suitability for isolation	Yes

## Complementary

[Ie] rated operational current	100 A at 415 V AC 50/60 Hz
[Ue] rated operational voltage	415 V AC 50/60 Hz
[Icm] rated short-circuit making capacity	5 kA switch-disconnector alone
[Icw] rated short-time withstand current	1500 A
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	6 kV
Control type	Toggle
Local signalling	ON/OFF indication
Contact position indicator	Yes
Mounting mode	Fixed
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom: YES
9 mm pitches	6
Height	85 mm
Width	54 mm
Depth	73 mm
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Connections - terminals</b>	Tunnel type terminals (top or bottom) - <= 1 x 50 mm <sup>2</sup> - rigid Tunnel type terminals (top or bottom) - <= 1 x 35 mm <sup>2</sup> - flexible Tunnel type terminals (top or bottom) - <= 1 x 35 mm <sup>2</sup> - flexible with ferrule
<b>Wire stripping length</b>	14 mm
<b>Tightening torque</b>	3.5 N.m

## Environment

<b>Standards</b>	IEC 60947-3 BS EN 60947-3 EN 60947-3 NZS 60947-3 AS 60947-3
<b>IP degree of protection</b>	IP20
<b>Pollution degree</b>	3
<b>Tropicalisation</b>	2
<b>Relative humidity</b>	95 % at 55 °C
<b>Ambient air temperature for operation</b>	-25...60 °C
<b>Ambient air temperature for storage</b>	-40...85 °C

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	4.800 cm
<b>Package 1 Width</b>	5.800 cm
<b>Package 1 Length</b>	8.200 cm
<b>Package 1 Weight</b>	251.000 g
<b>Unit Type of Package 2</b>	BB1
<b>Number of Units in Package 2</b>	4
<b>Package 2 Height</b>	8.000 cm
<b>Package 2 Width</b>	22.000 cm
<b>Package 2 Length</b>	9.500 cm
<b>Package 2 Weight</b>	1.055 kg
<b>Unit Type of Package 3</b>	S03
<b>Number of Units in Package 3</b>	44
<b>Package 3 Height</b>	30.000 cm
<b>Package 3 Width</b>	30.000 cm
<b>Package 3 Length</b>	40.000 cm
<b>Package 3 Weight</b>	11.950 kg

## Logistical informations

<b>Country of origin</b>	HU
--------------------------	----

## Contractual warranty

<b>Warranty (in months)</b>	18
-----------------------------	----



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint 150

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic No

[EU RoHS Directive](#) Compliant

SCIP Number E5f22bd9-8e0c-4771-b932-618a392a4c8b

REACH Regulation [REACH Declaration](#)

Halogen-free status Halogen free plastic parts product

## Use Longer

### Lifetime extension

Repair No

## Use Again

### Repack and remanufacture

End of life manual availability No need of specific recycling operations

Take-back No

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins