

CHERRY DW 5100



Models may vary from the image shown

Increased economics at every workplace.

CHERRY DW 5100 is the ideal wireless desktop set for those demanding the very best in terms of design, technology and ergonomics. The state-of-the-art desktop set from CHERRY for every workplace.

Key benefits

- Durable, high quality professional keyboard with 10 hotkeys
- Battery status display in keyboard and mouse
- Interference-free, wireless 2.4 GHz technology (with a range of approx. 5 m)
- Multi-station capability - operation of several wireless products in one room
- Easy to install, requiring no technical knowledge
- Ergonomic 5 button mouse, optimised for use with the right hand
- Infrared sensor and adjustable resolution (1000/1750 dpi)
- Nano USB receiver: also ideal for permanent use with the notebook
- Non-slip rubber on the sides
- Mouse has on/off switch for additional energy efficiency

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

black

Key colour:

black

Weight (product):

approx. 800 g (keyboard with battery), approx. 113 g (mouse with battery), approx. 3 g (receiver)

Total weight (with packaging):

approx. 1500 g

Transmission range:

approx. 8 m

Frequency range:

2.400 GHz - 2.4835 GHz

Storage Temperature:

-15°C to 60°C

Operating Temperature:

0°C to 40°C

Current Consumption:

max. 5 mA (keyboard), max. 15 mA (mouse), max. 35 mA (receiver)

Interface:

- USB

Product approvals:

- c-tick 
- CE 
- FCC 
- cTUVus 

System requirements:

- USB connection

Delivery Volume:

- 2 batteries (type AA)
- Operating instructions in hard copy
- 2 batteries (type AAA)
- 1 optical wireless mouse
- 1 wireless keyboard
- 1 nano USB transmission receiver

Dimensions (product):

467.7 x 171.5 x 21.6 mm (keyboard), 112.53 x 64.97 x 34.11 mm (mouse), 39.35 x 14 x 7.5 mm (receiver)

Packaging dimensions:

approx. 590 x 210 x 51 mm

Reliability:

- MTBF (90) > 80,000 hours

Mouse:

- Scanning: Infrared
- Resolution: 1000 / 1750 dpi (adjustable)
- Number of Keys: 5
- Mouse wheel design: Scroll wheel with key function
- Design: Ergonomic, Right-handed design
- Connection: USB
- Housing colour: black
- Key colour: black

Keyboard:

- Key technology: LPK
- Service life, standard key: > 10 million key operations
- Inscription layout: Standard
- Number of Keys: 105+10
- Number of additional keys: 10

Packaging Unit:

- Number of products in the master package: 6
- Number of master packages per pallet: 18

Warranty:

2 years

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)
1	CHERRY DW 5100	JD-0510CH-2	4025112085505	Switzerland
2	CHERRY DW 5100	JD-0510DE-2	4025112082979	Germany
3	CHERRY DW 5100	JD-0510FR-2	4025112083112	France
4	CHERRY DW 5100	JD-0510GB-2	4025112085277	UK
5	CHERRY DW 5100	JD-0510PN-2	4025112085499	Pan-Nordic