



Part Number: 3076F

Fieldbus, 1 Pr #18 Str TC, PO Ins, OS, PVC Jkt, Flexible SUN RES OIL RES

[Request Sample](#)

Product Description

Fieldbus, 1 Pair 18AWG (7x26) Tinned Copper, PO Insulation, Overall Beldfoil® Shield, Orange PVC Outer Jacket, Flexible SUN RES OIL RES

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
18	7x26	TC - Tinned Copper	0.045 in	1

Conductor Count:	2
Conductor Size:	18 AWG

Insulation

Material
PO - Polyolefin

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	20	7x28 mm

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.28 in

Construction and Dimensions

Cabling

Twists	Filler
5.3 twist/ft	Polypropylene

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
5.86 Ohm/1000ft	7.5 Ohm/1000ft

Capacitance

Max. Capacitance Unbalance	Nom. Capacitance Conductor to Shield	Nom. Mutual Capacitance
1.2 pF/ft	45 pF/ft	24 pF/ft

Inductance

Nominal Inductance
0.19 µH/ft

Impedance

Nominal Characteristic Impedance

100 Ohm

High Frequency (Nominal/Typical)

Nom. Insertion Loss

0.08 dB/100ft

Delay

Nominal Velocity of Propagation (VP) [%]

66 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Max./Min. Input Impedance (unFitted)
0.031 MHz	0.091 dB/100ft	100 Ohm

Current

Element	Max. Recommended Current [A]
Per Conductor	5.2 Amps

Voltage

UL Voltage Rating

300 V RMS

Electrical Characteristics Notes:	Max Propagation Delay Change From 7.812 kHz to 39.06 kHz: 518 pS/ft
Other Electrical Characteristic 2:	31.25 KBits/sec

Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-40°C To +105°C

Mechanical Characteristics

Oil Resistance:	Yes
UV Resistance:	Yes
Bulk Cable Weight:	38 lbs/1000ft
Max Recommended Pulling Tension:	60 lbs
Min Bend Radius/Minor Axis:	2.5 in

Standards

NEC Articles:	725, 727, 800
NEC/(UL) Specification:	CMR, ITC-ER, PLTC-ER
CEC/C(UL) Specification:	CMG
CPR Euroclass:	Eca
IEEE Specification:	1202, IEEE 383 Vertical Tray Flame Test (70,000 BTU)

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes - UL
Suitability - Indoor:	Yes
Suitability - Oil Resistance:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1666 Riser
IEEE Flammability:	1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
3076F 0061000	Blue, Light	C
3076F 0031000	Orange	C
3076F 003250	Orange	C
3076F 0032500	Orange	C
3076F 003500	Orange	C
3076F 0035000	Orange	C N
3076F 00310000	Orange	C N

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	N - FINAL PUT-UP LENGTH MAY VARY -0% TO +10% FROM LENGTH SHOWN.

Product Notes

Notes:	Fieldbus: Orange jacket. Profibus PA: Intrinsically Safe Blue jacket. Jacket diameter tolerance: +/- .010
--------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.