

# 64 32 120 ESD

## Electronics End Cutting Nippers ESD



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction hardened, cutting edge hardness at least 56 HRC
- With two-colour dual component grips, black/grey
- High-grade special tool steel, forged, multi stage oil-hardened
  - Style: Oblique End Cutter, short head, with small bevel,  $\alpha = 15^\circ$



### ESD pliers (electrostatic discharge)



electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

<b>Article No.</b>	64 32 120 ESD
<b>EAN</b>	4003773017844
<b>Head</b>	mirror polished
<b>Handles</b>	with multi-component grips
<b>Style</b>	3
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	1,0
<b>Cutting capacities hard wire (diameter) Ø mm</b>	0,5
<b>Cutting capacities soft wire (diameter) Ø mm</b>	1,5
<b>B mm</b>	10,0
<b>D mm</b>	7,0
<b>C mm</b>	17,0
<b>A mm</b>	11,0
<b>Dimensions angle °</b>	15
<b>Nominal size</b>	120 mm
<b>Length mm</b>	120
<b>Net weight g</b>	92

technical change and errors excepted

