

## Features

- Double Shut Off
- Maximum Operating Pressure 1000 Bar
- Ball Lock
- Operating Temperature from -30 °C to +100 °C
- Steel
- Plastic Dust Plug Included
- Interchangeable:

CEJN 115  
CEJN 115FF

## RS PRO Hydraulic Quick Connect Couplings

RS Stock No.: 0727374



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

The RS PRO 85 Series hydraulic quick connect couplings are heavy-duty designed for demanding hydraulic applications. Here are the key features:

Here are the key features:


- **Screw-to-Connect Design**  
Ensures secure, vibration-resistant connections, ideal for high-pressure and pulsating hydraulic circuits
- **High Pressure Capability**
- **Robust Construction**
- **Non-Spill Valve System**  
Prevents fluid leakage during disconnection, reducing contamination and environmental hazards.
- **Safety Locking Mechanism**  
Screw connection ensures positive locking, preventing accidental release under load
- **Dust Plug for Coupling**

Applications: **construction machinery, agricultural equipment, oil & gas, and industrial hydraulic systems** where high pressure and vibration resistance are critical.

Attention: The Coupler and plug should not be loaded before connection

Interchangeability:

- CEJN 115
- CEJN 115FF



Female Threaded Shut-Off Coupler



T Connection	Ø D (mm)	L (mm)
G 3/8"	27	63.5

## Specifications

<b>Manufacturer Series</b>	85
<b>Compatible with</b>	CEJN 115 CEJN 115FF
<b>Maximum Operating Pressure</b>	1000 Bar
<b>Minimum Operating Temperature</b>	-30 °C
<b>Maximum Operating Temperature</b>	+100 °C
<b>Type</b>	Quick Connect Coupling
<b>Locking Style</b>	Ball Lock
<b>Double Shut Off</b>	Double Shut Off
<b>Thread Size</b>	3/8 in
<b>Thread Standard</b>	G
<b>Thread Gender</b>	Female
<b>Coupling Gender</b>	Female
<b>Thread</b>	G 3/8 in Female
<b>Material</b>	Steel
<b>Finish</b>	Free-cutting steel
<b>Seal Material</b>	Nitrile Rubber
<b>Sleeve Material</b>	Steel
<b>Valve Material</b>	Steel
<b>Spring Material</b>	14310
<b>Locking O Ring Material</b>	AISI-316

