

KMV 44X9,6 - Cable marker



0812007

<https://www.phoenixcontact.com/gb/products/0812007>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Stainless steel label, silver, unlabeled, can be labeled with: P1 ENGRAVING UNIT, ENGRAVING UNIT, cable diameter range: 1 ... 63 mm, mounting type: Assembly with cable ties, Number of individual labels: 1, text field height: 9 mm, text field width: 23 mm

Your advantages

- Easy assembly with UNIFOX-CT M7,9
- Secured using stainless steel cable binders
- Cable markers for marking cables and conductors with larger cross sections
- The individual stainless steel markers are pushed onto the corresponding holders

Commercial data

Item number	0812007
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG2415
Product key	BG2415
Catalog page	Page 247 (C-3-2019)
GTIN	4017918932145
Weight per piece (including packing)	735 MGM
Weight per piece (excluding packing)	735 MGM
Customs tariff number	73269098
Country of origin	US

KMV 44X9,6 - Cable marker

0812007

<https://www.phoenixcontact.com/gb/products/0812007>



Technical data

Product properties

Product type	Conductor marking
Type	Mounting set

Marking

Number of individual labels	1
-----------------------------	---

Dimensions

Width	9.6 mm
Length	44 mm

External dimensions

Outside diameter	1 mm ... 63 mm
------------------	----------------

Text field

Text field width	23 mm
Text field height	9 mm

Material specifications

RoHS compliant	yes
Color	silver
Material	Stainless steel

Cable/line

External cable diameter	1 mm ... 63 mm
-------------------------	----------------

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-80 °C ... 538 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

KMV 44X9,6 - Cable marker



0812007

<https://www.phoenixcontact.com/gb/products/0812007>

Classifications

ECLASS

ECLASS-12.0	27281102
ECLASS-13.0	27281102

ETIM

ETIM 9.0	EC001530
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

KMV 44X9,6 - Cable marker



0812007

<https://www.phoenixcontact.com/gb/products/0812007>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk