



Main

Range of product	Canalis
Range compatibility	Canalis KS busbar trunking
Product or component type	Tap-off unit
Product compatibility	Canalis KS busbar trunking plug-in
[Ie] rated operational current	250 A at 35 °C
Fuse type	FuPacT ISFT switch-disconnector fuse: DIN fuse, size NH1
Provided equipment	Fuse
Mounting mode	Plug-in with auto-clamping system
Colour	White (RAL 9001)

Complementary

Device application	High power distribution
[Ue] rated operational voltage	500 V
[Ui] rated insulation voltage	500 V
Electrical connection	Cable gland - ISO63 (x2)
Standards	IEC 61439-1 IEC 61439-6
Body material	Metal

Environment

IP degree of protection	IP20 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	31 Cm
Package 1 Width	43.5 Cm
Package 1 Length	54 Cm
Package 1 Weight	16 Kg

Offer Sustainability

Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
EU RoHS Directive	Compliant with Exemptions EU RoHS Declaration
REACH Regulation	REACH Declaration
REACH Regulation	Reference contains Substances of Very High Concern above the threshold
EU RoHS Directive	Compliant By Exemption
Halogen-free status	Halogen free product
PVC free	Yes
Silicone-free	Yes
End of life manual availability	No need of specific recycling operations
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins