

STRATO-THERM DIAMOND GRIP


TE Internal #: 1-321897-5

Closed Ring Tongue Terminal, 22 – 16 AWG, #8 / M5 Stud, 5.2 mm
[.205 in] Stud Diameter, Closed Barrel, Straight, STRATO-THERM
DIAMOND GRIP

[View on TE.com >](#)



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 509 – 3260 CMA

Stud Size: #8, M5

Features

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M5
Sealable	No

Wire Insulation Support Retention Type	Insulation Support
--	--------------------

Configuration Features

Number of Holes	1
-----------------	---

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Unplated

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	5.2 mm[.205 in]



Tongue Thickness	.79 mm[.031 in]
Product Length	20.22 mm[.796 in]
Compatible Insulation Diameter (Max)	3.56 mm[.14 in]
Compatible Insulation Diameter Range	2.67 – 3.56 mm[.105 – .14 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Nickel
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



REPRESENTATION ONLY

TE Part # 46673
DAHT STRATO 22-16 ASSY



REPRESENTATION ONLY

TE Part # 46673-1
DAHT STRATO 22-16 ASSY

Also in the Series | STRATO-THERM DIAMOND GRIP



Knife Disconnects(3)



Ring Terminals(60)



Splices(8)


Customers Also Bought




TE Part #130014
TERM, R, PG, 22-16, M5



TE Part #5747150-4
09 RCPT SP/FMS STD



TE Part #770356-1
06P .062 COMM P&S RECPT




TE Part #1-2273111-4
M8 strgt socket to M12 strgt plug AA



TE Part #1-321897-0
DG 22-16 HT CHROMEL R 8



TE Part #353785-000
55A1121-24-9/96-9CS2275



TE Part #60618-6
CMNL PIN AUPHBZ L/P



TE Part #60617-6
CMNL SOK AUPHBZ L/P



Documents

Product Drawings

[DG 22-16 HT ALUMEL R M5](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1-321897-5_U.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-321897-5_U.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-321897-5_U.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.