



Cut protection

KRYTECH 832

Very high risk - ISO E



CUT PROTECTION
LEVEL E



ISO 13997:
24.3 N

DEXTERITY
EN ISO 21420:
5/5

Good protection for handling heavy and sharp metal parts in dry and slightly wet environments

SPECIFIC ADVANTAGES



Thermal protection

- Excellent thermal insulation of the hand



Comfort

- Added comfort, due to the gloves anatomical shape and the flexibility of the material



Durability

- Long service life even when faced with untrimmed metal



Productivity

- Good grip for picking up parts safely in oily environments, due to external leather layer



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Washability

- Dry cleaning: Up to 5 times to extend glove lifespan, reduce costs and waste

INDUSTRIES

- Automotive/mechanical industry

APPLICATIONS

- Cutting strips (plasma etc.)
- Handling parts post-press
- Handling sheet metal
- Handling untrimmed parts or sheet metal
- Metal working



Cut protection

KRYTECH 832

Very high risk - ISO E

LEGENDS

EN388 MECHANICAL HAZARDS						
PERFORMANCE LEVELS (X = NOT TESTED)						
4	X	4	3	E		
0-4	0-5	0-4	0-4	A-F	P	
Abrasion resistance						
Blade cut resistance						
Tear resistance						
Puncture resistance						
Cut resistance according to ISO 13997						
Impact protection (optional)						

EN407 THERMAL RISKS (HEAT AND FIRE)						
PERFORMANCE LEVELS (X = NOT TESTED)						
X	1	X	X	X	X	
0-4	0-4	0-4	0-4	0-4	0-4	
Limited flame spread						
Contact heat resistance						
Convective heat resistance						
Radiant heat resistant						
Small splashes of molten metal						
Resistance to large quantities of molten metal						

PRODUCT DETAILS

Interior finish	Seamless textile support from superior strength fibres
Gauge	10
Exterior finish	Leather layer on palm with reinforced thumb / index
Cuff characteristic	Knitted Cuff
Colour.s	Grey
European sizes	8 9 10 11

LOGISTIC DETAILS

Packaging	1 pair/bag 12 pairs/box 72 pairs/carton
-----------	---

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/01/19/0135
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE