

## 25U Adjustable Depth 4 Post Open Frame Server Rack Cabinet

**Product ID:** 4POSTRACK25



StarTech.com

The 4POSTRACK25 25U 4 Post Open Frame Rack provides a durable, open air housing for rackmount servers and networking equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The server rack features heavy gauge mounting rails to ensure a stable installation platform, with support for mounting depth adjustment (23.5 - 39.2 in.), giving you the flexibility to fit your rack-mounted equipment.

This 25U rack is compliant with EIA-RS-310C standards, offering a universal design that's compatible with equipment from popular manufacturers. Plus, the rack is flat-packed to reduce shipping costs and simplify handling.

For added versatility, StarTech.com offers an optional 4pc Caster Kit (4POSTCASTER) that can be installed on the bottom of the rack, making it easier to re-position the cabinet/rack as needed for future uses.

Backed by a StarTech.com lifetime warranty.

## Certifications, Reports and Compatibility

### Applications

- Durable storage for rackmount servers, KVM switches, and networking equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Audio/Video editing room, radio or television studio broadcast rackmount equipment

## Features

- 25U Open frame design
- Adjustable mounting depth from 18.3 - 39.2in
- Supports a weight capacity of up to 994.5lbs (450kg)
- Heavy gauge mounting rails
- Pre-drilled holes to secure the rack directly to the floor
- Unobstructed ventilation and cable routing
- Flat-packed for easy shipping
- TAA compliant for GSA Schedule purchases

---

### Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	25U
Special Features	Adjustable Mounting Rails
	Base Plate with Floor-Anchoring Holes
	Casters (Optional)
	Easy Assembly
Mounting Rail Profile	C-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

### Performance

Weight Capacity	994.5 lb [450 kg]
-----------------	-------------------

---

### Physical Characteristics

Color	Black
-------	-------



Construction Material      Steel

---

**Product Measurements**

Product Length	24.4 in [62 cm]
Product Width	22.5 in [57.1 cm]
Product Height	4.0 ft [1.2 m]
Weight of Product	84.2 lb [38.1 kg]
Maximum Mounting Depth	39.4 in [100 cm]
Minimum Mounting Depth	18.3 in [46.6 cm]
Product Height with Casters	4.3 ft [1.3 m]

---

**Packaging Information**

Flat Pack (Assembly Required)	Yes
Package Length	4.2 ft [1.3 m]
Package Width	25.1 in [63.8 cm]
Package Height	6.8 in [17.2 cm]
Shipping (Package) Weight	92.2 lb [41.7 kg]

---

**What's in the Box**

Included in Package	Front/Rear Frames
	Floor Plates
	Adjustable Horizontal Arms
	Floor Mounting Brackets
	M8 Hex Key
	M8x25 Hex Socket Screws
	M5x15 Truss Head Screws



Bushing Caps

M5 Screws

M5 Cage Nuts

---

***\*Product appearance and specifications are subject to change without notice.***

