

Driver Drill Brushless LXT®

DDF489

18V, 70 Nm, 0 – 1 800 min⁻¹

Model DDF489 driver drill is powered by 18V LXT® Li-Ion battery

The main features and benefits are: Excellent drilling capacity: Drilling in 2x timber with up to 1" ship auger bit in high speed mode, Robust keyless drill chuck with single metal sleeve, Metal gear housing.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 550 / 0 - 1800 min ⁻¹
Max. fastening torque Hard/Soft	73 / 40 Nm
Max Torque	110 Nm
Torque setting	21
Max. Drilling Diameter in Steel	13 mm
Driving Shank	1/2"-20UNF "
Drill Chuck Capacity	1,5 - 13 mm
Drilling Capacity Wood (Auger Bit)	38 mm
Drilling Capacity Wood (Self-feed bit)	51 mm
Vibration Level, Drilling into metal	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Drilling into metal	1,5 m/s ²
Sound Pressure Level (L _{pA})	77 dB(A)

User benefits

- Battery protection system automatically shuts off power when the battery level is low
- Keyless chuck for easy bit installation and removal
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Mechanical 2-speed gearing; High speed mode for speedy drilling in light duty applications; Low speed mode for heavy duty applications requiring high torque
- Electric brake for maximum productivity and increased operator safety
- Reversing switch is conveniently located

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing