


Rittal – The System.

Faster – better – everywhere.



AE 1011.600

Compact enclosures AE

State: 14/06/2022 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1011.600 - Compact enclosures AE Stainless steel

Compact enclosure AE in stainless steel including mounting plate.

Features

Model No.	AE 1011.600
Product modification	From August 2016, surface grinding will change from grain size 240 to grain size 400. The visually refined grinding finish will also enhance the enclosure's cleaning properties.
Material	Enclosure: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Sheet steel Stainless steel 1.4301 (AISI 304)
Surface finish	Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Supply includes	Enclosure with door(s) Mounting plate Lock: 3 mm double-bit
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 380 mm Height: 300 mm Depth: 210 mm
Mounting plate	Width: 334 mm Height: 275 mm
Number of doors	1
Number of locks	1
Lock	Lock version: Cam Number locks: 1 Lock insert: 3 mm double-bit Material lock: Die-cast zinc, nickel-plated

Features

Basic material	Stainless steel
Packs of	1 pc(s).
Weight/pack	8.4 kg
Copper weight (kg per piece)	0
Customs tariff number	94032080
EAN	4028177532328
ETIM 7.0	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	DNV-GL GOST Lloyds Register of Shipping RRR UL + C-UL
Certificates	IK-Code Protection category
Explanations	Declaration of conformity