

Fabric label - MM-EMLC (EX18)R C1 WH/BK - 0803936

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fabric label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Your advantages

- ✓ Enables labels to be stuck over edges and curves
- ✓ High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- ✓ The self-adhesive material in continuous format is particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- ✓ The material is cUL certified
- ✓ Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application
- ✓ The label material consists of a textile foil with very low restoring forces
- ✓ Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 212159
GTIN	4055626212159
Weight per Piece (excluding packing)	65.500 g
Custom tariff number	96121010
Country of origin	China
Sales Key	BG241E

Technical data

Dimensions

Length (b)	6000 mm
Width (a)	18 mm

Ambient conditions

Ambient temperature (operation)	0 °C ... 80 °C
---------------------------------	----------------

Fabric label - MM-EMLC (EX18)R C1 WH/BK - 0803936

Technical data

Ambient conditions

Recommended storage conditions	5 - 35°C / 30 - 80 % relative humidity. Storage in a cool and dry place in the original packaging is recommended.
--------------------------------	---

General

Color	white
Components	free from silicone, halogen, and cadmium
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	adhesive
Testing substances harmful to the wetting properties of lacquers (LABS conformity)	VW PV 3.10.7:2005-02
Result	Test passed
UV resistance	Following ISO 4892-2:2013-03
Result	Test passed
Test duration	96 h
Test for wipe resistance of inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Testing in a condensation changing climate in the presence of sulfur dioxide	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1,0 S
Cycles	2
Salt spray test	DIN EN 60068-2-11:2000-02
Result	Test passed

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27400629
eCl@ss 11.0	27281103
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27149100
eCl@ss 5.1	27141100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149129
eCl@ss 9.0	27400629

Fabric label - MM-EMLC (EX18)R C1 WH/BK - 0803936

Classifications

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 6.0	EC001288
ETIM 7.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE MH 48542
---------------	---	---	---------------