

# Product datasheet

Specifications



APC NetShelter Rack PDU  
Advanced Gen 2, Switched  
Metered Outlet, 3Phase, 22.1kW  
400V 32A or 17.3kW 415V 30A,  
530P6, 48 Outlet

APDU11350SM

## Main

|                           |                         |
|---------------------------|-------------------------|
| Colour                    | Black                   |
| Product or component type | PDU                     |
| PDU type                  | Switched metered outlet |
| Cord length               | 3 m                     |

## Complementary

|                             |                                  |
|-----------------------------|----------------------------------|
| Input Voltage               | 415 V 3 phases<br>400 V 3 phases |
| Height                      | 1780 mm                          |
| Width                       | 56 mm                            |
| Output Voltage              | 240 V                            |
| Depth                       | 75 mm                            |
| Product weight              | 9.6 kg                           |
| Mounting location           | Side                             |
| Mounting preference         | No preference                    |
| Input Plug Type             | IEC 60309 30 A 3P + N + PE       |
| mounting mode               | Rack-mounted                     |
| Rack units                  | 0U                               |
| Mounting position           | Vertical                         |
| Communication port protocol | 1000BASE-T<br>10/100BASE-T       |
| [In] rated current          | 24 A                             |
| permissible voltage         | 200...240 V<br>346...415 V       |
| Input current limits        | 30 A                             |
| Load capacity               | 17300 VA                         |
| Network frequency           | 50/60 Hz                         |
| Outlet type and quantity    | 24 C13/C15/C19/C21<br>24C13/C15  |

## Environment

|                        |      |
|------------------------|------|
| Product certifications | UKCA |
|------------------------|------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                       |                                                                                 |
|---------------------------------------|---------------------------------------------------------------------------------|
| Standards                             | UL 62368-1<br>CSA C22.2 No 62368-1<br>FCC part 15 Subpart B<br>CE<br>EN 62368-1 |
| IP degree of protection               | IP44                                                                            |
| Ambient air temperature for operation | -5...60 °C                                                                      |
| Relative humidity                     | 5...95 %                                                                        |
| Operating altitude                    | 0...10000 ft                                                                    |
| Ambient air temperature for storage   | -25...65 °C                                                                     |
| Storage Relative Humidity             | 5...95 %                                                                        |
| Storage altitude                      | 0...15240 m                                                                     |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 198 cm  |
| Package 1 Width              | 13.2 cm |
| Package 1 Length             | 26.2 cm |
| Package 1 Weight             | 12.6 kg |

## Logistical informations

|                   |    |
|-------------------|----|
| Country of origin | IE |
|-------------------|----|

## Contractual warranty

|                      |    |
|----------------------|----|
| Warranty (in months) | 36 |
|----------------------|----|



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better

| Materials and Substances               |                                                                                        |
|----------------------------------------|----------------------------------------------------------------------------------------|
| Packaging made with recycled cardboard | No                                                                                     |
| Packaging without single use plastic   | No                                                                                     |
| SCIP Number                            | 31346aed-552c-4a16-81d9-e683a383b6da                                                   |
| EU RoHS Directive                      | <a href="#">Compliant By Exemption</a>                                                 |
| REACH Regulation                       | <a href="#">Reference contains Substances of Very High Concern above the threshold</a> |

### Use Longer

| Lifetime extension |    |
|--------------------|----|
| Repair             | No |

### Use Again

| Repack and remanufacture |                                                                                                                             |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Removable battery        | No                                                                                                                          |
| Take-back                | No                                                                                                                          |
| WEEE Label               | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Image of product / Alternate images

Alternative

---



