



Data  
Technical Data

Input

Nominal input voltage $U_{i\text{ nom}}$	24 VDC
Input voltage range	18 ... 30 VDC

## Output

Total number of channels (module)	1
Nominal output voltage $U_{o\ nom}$	1 x 24 VDC
Output voltage range	18 ... 30 VDC ( $U_i$ – voltage drop)
Voltage drop	$\leq 80$ mV (4 A)
Nominal output current $I_{o\ nom}$	1 x 4 A (fixed setting)
Trip time	4 ms ... 100 s (Load-dependent)
Switch-on capacity	> 50000 $\mu$ F per channel
Switch-on behavior	Time-delayed channel switching (load-dependent, min. 170 ms / max. 500 ms)
Active Current Limitation	no

## Signaling and communication

Signaling	1 x LED status (green/yellow/rot/blue) 1 x cntrol input 1 x active signal output ( $U_i$ , max. 4 mA)
Operation status indicator	LED green (channel OK) LED red (tripped channel)
Remote input	18 ... 30 VDC signal, switches on/off and resets the channel

## Efficiency/Power losses:

Power loss $P_v$	$\leq 0.3$ W (no load)
Efficiency	$\geq 99$ %

## Fuse protection:

Internal fuse	T 15 A
---------------	--------

## Safety and protection:

Protection class	III
Degree of protection	IP20 (per EN 60529)
Reverse voltage protection	No
Transient protection, primary	Suppressor diode, 33 V
Parallel operation of single channels	Not permitted
Series connection	No
MTBF	1,258,733 h (per MIL-HDBK-217F2)



### Connection data

Number of jumper slots	8
Connection technology	Push-in CAGE CLAMP®
WAGO terminal	WAGO 857 Series
Solid conductor	0.08 ... 2.5 mm <sup>2</sup> / 28 ... 14 AWG
Fine-stranded conductor	0.34 ... 2.5 mm <sup>2</sup> / 22 ... 14 AWG
Strip length	9 ... 10 mm / 0.35 ... 0.39 Inch

### Geometrical Data

Width	6 mm / 0.236 inch
Height from upper-edge of DIN-35 rail	97.8 mm / 3.85 inch
Depth	94 mm / 3.701 inch

### Mechanical data

Type of mounting	DIN-35 rail (EN 60715)
------------------	------------------------

### Material Data

Weight	37.5 g
--------	--------

### Environmental Requirements

Surrounding air (operating) temperature	-25 ... 70 °C
Surrounding air (storage) temperature	-40 ... 85 °C
Relative humidity	10 ... 95 % (no condensation permissible)
Derating	No derating
Pollution degree	2

### Standards and specifications

Conformity marking	CE
Standards/specifications	EN 61000-6-2; EN 61000-6-3; UL 61010-2-201* (*pending)



**Commercial data**

Packaging type	bag
Country of Origin	DE
GTIN	4055143533591

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +91-120-4388700.