

LC7K06105B7

TeSys K contactor - 3P(3 NO) - AC-3 - <= 440 V 6 A
- 24 V AC coil



Main

| | |
|---------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range | TeSys |
| Product name | TeSys K |
| Device short name | LC7K |
| Contacteur application | Motor control |
| Utilisation category | AC-3 AC-4 |
| Poles description | 3P |
| Pole contact composition | 3 NO |
| [Ue] rated operational voltage | 690 V AC 50/60 Hz for power circuit <= 690 V AC 50/60 Hz for signalling circuit |
| [Ie] rated operational current | 6 A at <= 440 V AC AC-3 for power circuit |
| Motor power kW | 3 kW at 440 V AC 50/60 Hz 3 kW at 500...600 V AC 50/60 Hz 3 kW at 660...690 V AC 50/60 Hz 1.5 kW at 220...230 V AC 50/60 Hz 2.2 kW at 380...415 V AC 50/60 Hz 3 kW at 480 V AC 50/60 Hz |
| Control circuit type | AC 50/60 Hz silent |
| Control circuit voltage | 24 V AC 50/60 Hz |
| Auxiliary contact composition | 1 NO |
| [Uimp] rated impulse withstand voltage | 8 kV |
| Overvoltage category | III |
| [Ith] conventional free air thermal current | 20 A at <= 50 °C for power circuit 10 A at <= 50 °C for signalling circuit |
| Irms rated making capacity | 110 A AC for power circuit conforming to NF C 63-110 110 A AC for power circuit conforming to IEC 60947 110 A AC for signalling circuit conforming to IEC 60947 |
| Rated breaking capacity | 110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 110 A at 220...230 V conforming to IEC 60947 110 A at 380...400 V conforming to IEC 60947 70 A at 660...690 V conforming to IEC 60947 |
| [Icw] rated short-time withstand current | 90 A <= 50 °C 1 s power circuit 85 A <= 50 °C 5 s power circuit 80 A <= 50 °C 10 s power circuit 60 A <= 50 °C 30 s power circuit 45 A <= 50 °C 1 min power circuit 40 A <= 50 °C 3 min power circuit 80 A 1 s signalling circuit 90 A 500 ms signalling circuit 110 A 100 ms signalling circuit 20 A <= 50 °C >= 15 s power circuit |
| Associated fuse rating | 25 A gG at <= 440 V for power circuit 25 A aM for power circuit 10 A gG for signalling circuit conforming to IEC 60947 10 A gG for signalling circuit conforming to VDE 0660 |
| Average impedance | 3 mOhm at 50 Hz - Ith 20 A for power circuit |
| [Ui] rated insulation voltage | 690 V for power circuit conforming to IEC 60947-4-1 600 V for power circuit conforming to UL 508 690 V for signalling circuit conforming to IEC 60947-4-1 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

690 V for signalling circuit conforming to IEC 60947-5-1
 600 V for signalling circuit conforming to UL 508
 600 V for power circuit conforming to CSA C22.2 No 14
 600 V for signalling circuit conforming to CSA C22.2 No 14

| | |
|--------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Electrical durability | 1.3 Mcycles 6 A AC-3 at $U_e \leq 440$ V |
| Mounting support | Printed circuit boards |
| Standards | BS 5424 IEC 60947 NF C 63-110 VDE 0660 |
| Product certifications | CSA UL |
| Connections - terminals | Solder pins 1.5 x 0.9 mm |
| Operating time | 30 ms coil de-energisation and NO opening 30...40 ms coil energisation and NO closing |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 |
| Mechanical durability | 10 Mcycles |
| Operating rate | 3600 cyc/h |

Complementary

| | |
|---------------------------------|-------------------------------------------------------------------------------------------|
| Control circuit voltage limits | 0.85...1.1 U_c at ≤ 50 °C operational 0.1...0.75 U_c at ≤ 50 °C drop-out |
| Inrush power in VA | 3 VA at 20 °C |
| Hold-in power consumption in VA | 3 VA at 20 °C |
| Heat dissipation | 3 W |
| Auxiliary contacts type | Type instantaneous (1 NO) |
| Signalling circuit frequency | ≤ 400 Hz |
| Minimum switching current | 5 mA for signalling circuit |
| Minimum switching voltage | 17 V for signalling circuit |
| Non overlap distance | 0.5 mm |
| Insulation resistance | > 10 MOhm for signalling circuit |

Environment

| | |
|-------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| IP degree of protection | IP2x conforming to VDE 0106 |
| Protective treatment | TC conforming to IEC 60068 TC conforming to DIN 50016 |
| Ambient air temperature for storage | -50...80 °C |
| Operating altitude | 2000 m without derating in temperature |
| Flame retardance | V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102 |
| Mechanical robustness | Shocks contactor closed, on X axis 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Y axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Z axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on X axis 6 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Y axis 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Z axis 10 Gn for 11 ms IEC 60068-2-27 Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor opened 2 Gn, 5...300 Hz IEC 60068-2-6 |
| Depth | 57 mm |
| Product weight | 0.225 kg |

Offer Sustainability

| | |
|----------------------------------|-----------------------------------------------------------------------|
| Sustainable offer status | Not Green Premium product |
| RoHS | Compliant - since 0825 - Schneider Electric declaration of conformity |
| Product end of life instructions | Need no specific recycling operations |

