

RND
components

- No burrs and sharp edges
- 1018~1022 carbon steel material
- Trivalent blue zinc 3.8 μm finish
- Heat treat: case harden surface HV 450~560, core HV 290~370
- Material and finish comply with 211/65/EU (RoHS)
- Meets DIN 7985 standard

Length	L
3	2.8~3.2
4	3.75~4.25
5	4.75~5.25
6	5.75~6.25
8	7.70~8.30
10	9.70~10.30
12	11.65~12.35
14	13.65~14.35
16	15.65~16.35
20	19.58~20.42
25	24.58~25.42
30	29.58~30.42
35	34.5~35.5
40	39.5~40.5
45	44.5~45.5
50	49.5~50.5
55	54.4~55.6
60	59.4~60.6

[illegible]

Thread (6g)	DK Head Diameter	K Head Height	Six-lob Recess	T(Max)	Thread (D)	Thread (C)	N(Min)
M3x0.5	5.70~6.00	2.28~2.52	T10	1.20	2.88~2.97	2.98~3.07	0.60
M4x0.7	7.64~8.00	2.95~3.25	T20	1.90	3.84~3.94	3.98~4.08	1.00

