

## FEATURES

- **2.5 m Cable Length:**  
Provides ample reach for connecting devices without the need for extensions
- **IEC C19 to CEE 7 Connectors:** Compatible with a wide range of equipment and power sources
- **16 A Current Rating:**  
Supports high-power devices, ensuring efficient performance
- **250 V Voltage Rating:**  
Suitable for standard voltage requirements in industrial settings
- **Black Polyvinyl Chloride Jacket:** Offers durability and protection against environmental factors
- **Straight Plug and Socket Type:** Simplifies installation and connection

## RS PRO 2.5 m Power Cable, IEC C19 to CEE 7

RS Stock No: 558-924



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO power cable is designed for reliable and efficient power transmission in various industrial and commercial settings. With a length of 2.5 metres, it offers flexibility and convenience for connecting devices to power sources. The cable is equipped with an IEC C19 connector on one end and a CEE 7 connector on the other, making it suitable for a range of applications. Its robust construction ensures durability and safety, meeting multiple international standards.

## General Specifications

Connector Type A	IEC C19
Connector Type B	CEE 7
Jacket Colour	Black
Mains Socket Type	Straight
Product Type	Power Cable

## Mechanical Specifications

Cable Length	2.5 m
Jacket Material	Polyvinyl Chloride

## Electrical Specifications

Current Rating	16 A
Mains Plug Type	Straight
Voltage	250 V

## Approvals

Standards/Approvals	CCCs, CEBEC, CSA, D, EAC, ENEC 11, FI, ICC, IMQ, JET, KEMA, KEUR, N, NF, OVE, PSE, R31947, RCM N10544, S, UL, VDA
---------------------	---