

LGET 2

SKF Extreme Temperature, Extreme Condition Bearing Grease

SKF LGET 2 is a synthetic fluorinated oil based grease, using a PTFE thickener. It is especially suitable for applications at extremely high temperatures from 200 °C (390 °F) up to 260 °C (500 °F).

- Long life in aggressive environments such as very reactive areas with a presence of high purity gaseous oxygen and hexane
- Excellent oxidation resistance
- Good corrosion resistance
- Excellent water and steam resistance

Typical applications:

- Bakery equipment (ovens)
- Kiln truck wheels
- Load rollers in copying machines
- Wafer baking machines
- Textile dryers
- Film stretching tenders
- Electric motors running at extreme temperatures
- Emergency / hot fans
- Vacuum pumps



Important note:

LGET 2 is a fluorinated grease and is not compatible with other greases, oils and preservatives. Therefore, very thorough cleaning of bearings and systems is essential before applying fresh grease (except when reapplying LGET 2).



Technical data

Designation	LGET 2/(pack size)
DIN 51825 code	KFK2U-40
NLGI consistency class	2
Soap type	PTFE
Colour	Whitish cream
Base oil type	Synthetic (fluorinated polyether)
Operating temperature range	-40 to +260 °C (-40 to +500 °F)
Dropping point DIN ISO 2176	>300 °C (>570 °F)
Base oil viscosity	
40 °C, mm ² /s	400
100 °C, mm ² /s	38
Penetration DIN ISO 2137	
60 strokes, 10 ⁻¹ mm	265–295
Mechanical stability	
Roll stability, 50 hrs at 80 °C, 10 ⁻¹ mm	±30 max. 130 °C (265 °F)

Corrosion protection	
Emcor: – standard ISO 11007	1–1
Water resistance	
DIN 51 807/1, 3 hrs at 90 °C	0 max.
Oil separation	
DIN 51 817, 7 days at 40 °C, static, %	13 max. 30 hrs at 200 °C (390 °F)
Copper corrosion	
DIN 51 811, 110 °C	1
Rolling bearing grease life	
ROF test	>700, 5 600 r/min.*
L ₅₀ life at 10 000 r/min., hrs	at 220 °C (430 °F)
EP performance	
4-ball test, welding load DIN 51350/4, N	8 000 min.
Available pack sizes	
	50 g (25 ml) syringe 1 kg

* Typical value



SKF lubricants offer major competitive advantages:

- Designed and tested to outperform under real conditions
- Product data include specific test results enabling a better selection
- Strict quality control of every production batch help ensure consistent performance
- Quality control allows SKF to offer a five-year shelf-life* from the date of production



Production processes and raw materials vastly influence grease properties and performance. It is virtually impossible to select or compare greases based only on their composition. Therefore, performance tests are needed to provide crucial information. In over 100 years, SKF has accrued vast knowledge about the interaction of lubricants, materials and surfaces.



This knowledge has led SKF, in many cases, to set industry standards in bearing lubricant testing. Emcor, ROF, ROF+, V2F, R2F and Bequiet are just some of the multiple tests developed by SKF to assess the performance of lubricants under bearing operating conditions. Many of them are widely used by lubricant manufacturers worldwide.

* SKF LGFP 2 food grade grease offers a two-year shelf-life from the date of production

© SKF is a registered trademark of the SKF Group.

© SKF Group 2013

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB MP/P8 12046 EN · December 2013

