


O5S700



Through-beam laser sensor transmitter

O5SLOOKG/US100



- 1 When a M5 mounting screw is used, the max. tightening torque is 2 Nm.
2 light emission



Product characteristics

Type of light	red light
Laser protection class	1
Housing	rectangular

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	13
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	655

Detection zone

Transmitter / receiver		transmitter
Range	[m]	< 60
Range adjustable		no
Max. light spot diameter	[mm]	150

O5S700



Through-beam laser sensor transmitter

O5SLOOKG/US100

Light spot dimensions refer to _____ at maximum range

Operating conditions

Ambient temperature [°C] _____ -10...60

Protection _____ IP 67

Tests / approvals

EMC _____ EN 60947-5-2 _____

Laser protection class _____ 1

Notes on laser protection _____ Caution: _____ laser light

_____ laser class: _____ 1

_____ EN / IEC60825-1:2007

_____ EN / IEC60825-1:2014

_____ Complies with 21 CFR 1040 except for deviations pursuant to Laser Notice No. 50, dated June 2007.

MTTF [years] _____ 1038

Mechanical data

Weight [g] _____ 67

Housing _____ rectangular

Dimensions [mm] _____ 56 x 18.2 x 46.8

Materials _____ housing: PA; bezel: stainless steel; operator interface: TPU

Lens material _____ PMMA

Lens alignment _____ side lens

Displays / operating elements

Display _____ operation _____ 1 x LED, green

Remarks

Remarks _____ operating voltage "supply class 2" according to cULus

Pack quantity _____ 1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



O5S700



Through-beam laser sensor transmitter

O5SLOOKG/US100

Connection

