
Parker Product Datasheet



High Pressure No-Skive fitting 70 series for High Pressure No-Skive three wire braided Compact and Multispiral hydraulic hoses.

PART NUMBER: 16F70-16-16-1P
HOSE INSIDE DIAMETER: -16
PORT SIZE: 1'
CONNECTION 2 TYPE: SAE Code 62 Flange Head
PORT TYPE: SFS
SHAPE: Elbow 45°

PRODUCT OVERVIEW

Parker's Parkrimp No-Skive high pressure fittings 70 series are permanent, crimp style hydraulic fittings that allow a quick assembly with our family of Parkrimp crimpers. Assembly of No-Skive hose and fittings does not require removal of the outer cover of the hose. This eliminates premature hydraulic hose failure caused by skiving too long or short. 70 series fittings have chromium-6-free plating and are used with Parker No Skive Compact 3-wire braid hydraulic hoses and No Skive four wire multispiral hydraulic hose.
Parker Hannifin also meets the requirements of SAE J1273 and ISO 17165-2, which pay particular attention to matching the hose with the fittings and to their compatibility proven by the manufacturer.

Markets:
· Construction Equipment
· Transportation
· Forestry

· Agriculture

Features / Benefits:
· Matched hose and fitting system guarantees an approved and safe combination
and the highest quality and safety combined with the longest service life of the final product to the end-users.
· No-Skive technology offers the easiest and most efficient and safe production process to the assemblers.

Applications:
· All construction equipment machines
· Agriculture and forestry machines
· general high pressure hydraulic applications

Parker Parkrimp high pressure fittings 70 series are compatible with the following hoses:
· 371LT, 372, 372RH and 372TC
· 701

TECH SPECIFICATIONS

FOR FLUID TYPE	Air (General Industrial Air)
DROP LENGTH	32 mm (see drawing legend E)
FOR FLUID TYPE	Hydraulic Fluids on Mineral-oil Basis
SHAPE	Elbow 45°
CONNECTION LENGTH	74 mm (see drawing legend B)
FOR FLUID TYPE	Lubricants
FITTING LENGTH	119 mm (see drawing legend A)
SPECIFICATIONS MET	ISO 12151-3-E45-S
DIVISION	Polymer Hose Division Europe
FOR FLUID TYPE	Coolants (Glycol, Water-Glycol)
CONFIGURATION	Hose to Port
FOR FLUID TYPE	Water
FOR FLUID TYPE	Mineral Hydraulic Oil

DIVISION	Polymer Hose Division Europe
FLANGE SIZE	48 mm (see drawing legend F)
MAXIMUM OPERATING PRESSURE	420 bar
FOR FLUID TYPE	Lubricants (Oils)
CONNECTION 2 TYPE	Code 62 Flange
INDUSTRY	Off-road Machinery
MAXIMUM OPERATING PRESSURE	42.0 MPa
BODY MATERIAL	Steel
FOR FLUID TYPE	Air
TECHNOLOGY	Fluid & Gas Handling
CONNECTION 2 TYPE	SAE
PRODUCT TYPE	Crimp Fittings No-Skive
CONNECTION 1 SIZE	-16 (Size)
PORT TYPE	SFS
INDUSTRY	Transportation
CONNECTION 1 TYPE	Hose
CONNECTION 1 SIZE	25.4 mm Hose I.D.
BRAND	Parker
CONNECTION 2 SIZE	1 inch
CONNECTION 2 TYPE	Flange
APPLICATION	High Pressure Hydraulics
CONNECTION 1 SIZE	1 inch Hose I.D.