

Features

- **Secure Lockout for Plug Valves** – Effectively locks manually operated plug valves to prevent accidental activation during maintenance.
- **Wide Stem Compatibility** – Suitable for valve stem diameters ranging from **9.5 mm to 22.20 mm**, covering a broad range of valve sizes.
- **Durable Polypropylene Construction** – Made from tough, **impact-resistant polypropylene** for long-term performance in industrial environments.
- **Weather & Chemical Resistance** – Built to withstand harsh conditions, making it suitable for both indoor and outdoor applications.
- **Compact & Easy to Use** – Lightweight and **user-friendly design** enables fast and efficient lockout without disrupting workflow.
- **Highly Visible Design** – Bright color ensures the lockout is clearly seen, enhancing safety compliance on-site.

RS PRO Plug Valve Lockout (9.50 mm - 22.20 mm)

RS Stock No.: 0710526



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Compact and durable lockout device specifically designed for plug valves.*
- *Compatible with stem diameters ranging from 9.5 mm to 22.20 mm.*
- *Constructed from **robust polypropylene**, offering excellent resistance to environmental stress.*
- ***Highly visible** design enhances on-site safety awareness.*
- *Easy to install and securely attaches without interfering with valve function once removed.*
- *Ideal for **industrial maintenance teams** needing reliable valve lockout during servicing.*
- *Supports compliance with workplace **safety protocols and lockout/tagout (LOTO) standards.***

General Specifications

Type	Plug Valve Lockout
Material	ABS with stainless steel clamp
Colour	Red
Package	PE-LD

Mechanical Specifications

Weight	80 Grams
--------	----------

Operation Environment Specifications

Withstand temperature	-31°C to + 93°C (-25°F to + 200°F)
-----------------------	------------------------------------