HAW Air Warmer

CDimplexcommercial

A world of expertise



HAW1000N

- Heavy duty robust case for long life and reliable operation.
- Finned design giving large surface area for optimum heating performance
- Supplied with guard as standard
- Designed use in industrial locations where robust heating is needed.

Technical Details

Construction / Finish:

Cast Iron body

Black stove enamel finish

Black wire guard

Element:

Metal Sheathed

Safety:

Manual reset thermal cut-out

Installation:

Floor fixing through heater fixing points Separate wire guard supplied for use

with the heater

Cable entry:

20mm metal cable gland

Warranty:


12 months

Range Details



Model	HAW1000N
Output (kW)	1.0
Supply	220—240v 1PN
Fixing Width	449mm
Fixing Depth	179mm
Weight	14kg

Additional Information



Additional Information

Guard width (mm) Guard fixing width (mm)	663mm 674mm
Guard depth (mm) Guard fixing depth (mm)	364mm 229mm

