

SSM3A325P7

pre Assembled, Harmony Solid State Relays,
25A, DIN rail mount, zero voltage switching,
input 180...280V AC, output 48...600V AC

Main

Range of product	Harmony Solid State Relays
Device short name	SSM3
Product or component type	Modular DIN rail relay
Number of channels	3
Number of phases	3 phases
Output switching mode	Zero voltage switching

Complementary



Mounting support	Symmetrical DIN rail
[In] rated current	25 A
Output voltage	48...600 V AC
[Uc] control circuit voltage	180...280 V AC
Tightening torque	0.6...0.7 N.m for input 1.36...1.7 N.m for output
Connections - terminals	Screw terminals: 0.2...1.3 mm ² , (AWG 24...AWG 16) for input Screw terminals: 1.3...5.3 mm ² , (AWG 16...AWG 10) for output
Maximum capacitance	8 pF for input/output
Insulation resistance	1000 MOhm
Local signalling	LED (green) for input status
Switching voltage	10 V turn-off 180 V turn-on
Input current	19...24 mA
Solid state output type	Zero voltage switching
Load current	0.1...25 A
Transient overvoltage	1100 V
Surge current	286 A for 20 ms at 50 Hz 300 A for 16.6 ms at 60 Hz
Maximum voltage drop	<1.35 V on-state
Motor power hp	1 Hp 40 °C 240 V AC 2 Hp 40 °C 380 V AC 3 hp 40 °C 480 V AC
Maximum I ² t for fusing	410 A ² .S for 10 ms at 50 Hz 374 A ² .s for 8.3 ms at 60 Hz
Maximum leakage current	0.25 mA off-state
DV/dt	500 V/μs off-state at maximum voltage
Response time	30 ms (turn-off) 20 ms (turn-on)
Power factor	0.5 (with maximum load)
Overvoltage category	III
Width	90 mm
Test button	Without test button
Net weight	0.74 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Dielectric strength	4 KV AC for input/output 4 kV AC for input or output to case
Pollution degree	2
Standards	UL 508 IEC 60950-1 CSA C22.2 No 14
Product certifications	CSA[RETURN]UL[RETURN]EAC
Marking	CSA CE EAC UL
IP degree of protection	IP20
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...100 °C

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration