

## SURFACE MOUNT SCHOTTKY BARRIER RECTIFIERS

REVERSE VOLTAGE - 45Volts  
FORWARD CURRENT - 15.0 Amperes


### FEATURES

- Very low profile - typical height of 1.1 mm
- Ideal for automated placement
- Trench Schottky technology
- Low forward voltage drop, low power losses
- High efficiency operation
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Compliant to RoHS Directive 2002/95/EC and in accordance to WEEE 2002/96/EC

### MECHANICAL DATA

- Case: TO-277A (SMPC)
- Molding compound meets UL 94 V-0 flammability rating
- Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

### TO-277A



Dimensions in inches and (millimeters)

### MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%

CHARACTERISTICS		SYMBOL	S15P45	UNIT		
Maximum Recurrent Peak Reverse Voltage		V <sub>RRM</sub>	45	V		
Maximum DC Forward Current		I <sub>F</sub> <sup>(1)</sup>	15	A		
		I <sub>F</sub> <sup>(2)</sup>	4.8			
Peak Forward Surge Current 10ms Single Half Sine-Wave Superimposed on Rated Load		I <sub>FSM</sub>	210	A		
Instantaneous Forward voltage	I <sub>F</sub> =5.0A	T <sub>A</sub> =25°C	0.40(TYP.)		V	
			I <sub>F</sub> =7.5A	0.45(TYP.)		
	I <sub>F</sub> =15A	0.49(TYP.)	0.58(MAX.)			
	I <sub>F</sub> =5.0A	T <sub>A</sub> =125°C	0.31(TYP.)			
			I <sub>F</sub> =7.5A	0.34(TYP.)		
			I <sub>F</sub> =15A	0.42 (TYP.)		0.51 (MAX.)
Reverse Current	V <sub>R</sub> =45V	T <sub>A</sub> =25°C	1500 (MAX.)		μA	
		T <sub>A</sub> =125°C	15 (TYP.)	50 (MAX.)	mA	
Typical Thermal Resistance		R <sub>θJA</sub> <sup>(5)</sup>	75		°C/W	
		R <sub>θJM</sub> <sup>(6)</sup>	4			
Operating Temperature Range		T <sub>J</sub>	-55 to +150		°C	
Storage Temperature Range		T <sub>STG</sub>	-55 to +150		°C	

Notes:(1) Mounted on 30 mm x 30 mm pad areas aluminum PCB

(2) Free air, mounted on recommended copper pad area

(3)Pulse test: 300 μs pulse width, 1 % duty cycle

(4) Pulse test: Pulse width ≤ 40 ms

(5) Free air, mounted on recommended copper pad area; thermal resistance R<sub>θJA</sub> - junction to ambient

(6) Mounted on 30 mm x 30 mm aluminum PCB; thermal resistance R<sub>θJM</sub> - junction to mount

(7).The typical data above is for reference only(典型值仅供参考).

FIG.1-TYPICAL TRANSIENT THERMAL IMPEDANCE PER DIODE




FIG.3-FORWARD POWER LOSS CHARACTERISTICS PER DIODE




FIG.5-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS PER DIODE




FIG.2-TYPICAL REVERSE LEAKAGE CHARACTERISTICS PER DIODE




FIG.4-TYPICAL JUNCTION CAPACITANCE





FIG.6-FORWARD CURRENT DERATING CURVE



NOTE: (1) Mounted on 30 mm x 30 mm aluminum PCB; TM measured at the terminal of cathode band ( $R_{\theta JM} = 4 \text{ } ^\circ\text{C/W}$ )  
(2) Free air, mounted on recommended copper pad area ( $R_{\theta JA} = 75 \text{ } ^\circ\text{C/W}$ )